

# IB IL 230 PWR IN - Inline function terminal



2740339

<https://www.phoenixcontact.com/us/products/2740339>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline power terminal block, without accessories, without fuse, 230 V AC

## Product description

The terminal is designed for use within an Inline station. The terminal enables the 230 V AC supply voltage to be fed into a 230 V AC area of the Inline station. An end terminal, which must be used to terminate the 230 V AC area, is supplied as standard with the feed-in terminal.

## Your advantages

- Diagnostic and status indicators
- Supplying the L phase (230 V AC)

## Commercial data

Item number	2740339
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRI121
GTIN	4017918465643
Weight per piece (including packing)	164.5 g
Weight per piece (excluding packing)	164.5 g
Customs tariff number	85389091
Country of origin	DE

## Technical data

### Product properties

Type	modular
	Inline

### Insulation characteristics

Protection class	I (IEC 61140, EN 61140, VDE 0140-1)
------------------	-------------------------------------

### System properties

#### Programming data

ID code (dec.)	none
Register length (bus)	0 bit

### Electrical properties

Test section	5 V supply, incoming remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	5 V supply, outgoing remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
	7.5 V supply (bus logics) / I/O area 120 V AC 2500 V AC 50 Hz 1 min
	Routine test 1200 V AC 50 Hz 1 min
	I/O area 120 V AC/PE 500 V AC 50 Hz 1 min
	Output / Phase 500 V AC 50 Hz 1 min

### Supply

I/O voltage	230 V AC
I/O voltage range	207 V AC ... 253 V AC (including all tolerances, including ripple)
Residual ripple	± 23 V
Max. current consumption	8 A

### Connection data

#### Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16

### Interfaces

#### Inline local bus

Connection method	Inline data jumper
-------------------	--------------------

### Dimensions

# IB IL 230 PWR IN - Inline function terminal

2740339

<https://www.phoenixcontact.com/us/products/2740339>

Dimensional drawing	
Width	36.6 mm
Height	119.8 mm
Depth	71.5 mm

## Material specifications

Color	gray
-------	------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	75 % ... 85 %
Permissible humidity (storage/transport)	75 % ... 85 %

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IB IL 230 PWR IN - Inline function terminal

2740339


<https://www.phoenixcontact.com/us/products/2740339>

## Drawings

Dimensional drawing



Connection diagram



# IB IL 230 PWR IN - Inline function terminal



2740339

<https://www.phoenixcontact.com/us/products/2740339>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)