

# SUBCON-PLUS-PROFIB/AX - D-SUB bus connector



2744377

<https://www.phoenixcontact.com/us/products/2744377>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



D-SUB connector, 9-pos., male connector, axial version with two cable entries, bus system: PROFIBUS DP up to 12 Mbps, termination resistor can be switched on via slide switch, pin assignment: 3, 5, 6, 8; spring-cage connection terminal blocks

## Product description

The D-SUB series, SUBCON-PLUS-PROFIB/... was specially designed for use in PROFIBUS systems up to 12 Mbps. Under field conditions, it allows convenient and fast connection of the incoming and outgoing bus cable. The terminating resistor is already integrated in all versions. It can be connected externally by means of a slide switch. At the same time, the outgoing bus segment is switched off. This makes it easy to start up segment by segment while incorrect terminations are avoided.



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2744377       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DN10          |
| Product key                          | DNC531        |
| GTIN                                 | 4017918818135 |
| Weight per piece (including packing) | 37.5 g        |
| Weight per piece (excluding packing) | 53 g          |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# SUBCON-PLUS-PROFIB/AX - D-SUB bus connector



2744377

<https://www.phoenixcontact.com/us/products/2744377>

## Technical data

### Notes

#### Note on application

|                     |                         |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

#### Utilization restriction

|            |   |
|------------|---|
| CCCex note | Use in potentially explosive areas is not permitted in China. |
|------------|---|

### Product properties

|                |  |
|----------------|--|
| Product type   | Data plug  |
| MTTF           | 6706 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)    |
|                | 1817 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%) |
|                | 155 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)    |
| Pin assignment | 3, 5, 6, 8   |

### Electrical properties

|   |         |
|---|---------|
| Maximum power dissipation for nominal condition | 0.025 W |
| Nominal voltage $U_N$                           | 5 V     |
| Nominal current $I_N$                           | 100 mA  |
| Transmission medium                             | Copper  |

### Connection data

|                   |            |
|-------------------|------------|
| Tightening torque | ... 0.4 Nm |
|-------------------|------------|

#### D-SUB connection

|                   |                 |
|-------------------|-----------------|
| Connection method | D-SUB connector |
|-------------------|-----------------|

#### PCB connection

|  |                        |
|--|------------------------|
| Connection method                          | Spring-cage connection |
| Stripping length                           | 9 mm                   |
| Conductor cross-section, rigid min.        | 0.12 mm <sup>2</sup>   |
| Conductor cross-section, rigid max.        | 0.5 mm <sup>2</sup>    |
| Single-wire/terminal point, rigid AWG min. | 26                     |
| Single-wire/terminal point, rigid AWG max. | 20                     |

### Interfaces

|            |             |
|------------|-------------|
| Bus system | PROFIBUS DP |
| Signal     | PROFIBUS    |


### Dimensions

# SUBCON-PLUS-PROFIB/AX - D-SUB bus connector



2744377

<https://www.phoenixcontact.com/us/products/2744377>

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 17 mm  |
| Height              | 31.5 mm  |
| Length              | 58.2 mm  |

## Material specifications

|                    |                            |
|--------------------|----------------------------|
| Color (Housing)    | white aluminium (RAL 9006) |
| Material (Housing) | ABS (metal-plated)         |

## Cable/line

|                         |                                       |
|-------------------------|---------------------------------------|
| External cable diameter | 7.6 mm ... 8.4 mm (Incoming bus line) |
|-------------------------|---------------------------------------|

## Mechanical properties

### Mechanical data

|                             |          |
|-----------------------------|----------|
| Insertion/withdrawal cycles | > 200    |
| Fixing screws               | 4-40 UNC |
| Tightening torque           | 0.4 Nm   |

## Mechanical tests

|  |  |
|--|--|
| Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6 | : 5g, 10...150 Hz, 2.5 h, in XYZ direction |
| Shock in accordance with EN 60068-2-27/IEC 60068-2-27              | : 15g, 11 ms period, half-sine shock pulse |

## Environmental and real-life conditions

### Ambient conditions

|  |  |
|--|--|
| Degree of protection                     | IP40   |
| Ambient temperature (operation)          | -20 °C ... 75 °C   |
| Ambient temperature (storage/transport)  | -25 °C ... 80 °C   |
| Altitude                                 | ≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation) |
| Permissible humidity (operation)         | 10 % ... 95 % (non-condensing)   |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing)  |

## Approvals

### ATEX

|                |                          |
|----------------|--------------------------|
| Identification | Ⓔ II 3 G Ex ec IIC T4 Gc |
| Certificate    | PxCIF15ATEX2744348X      |

# SUBCON-PLUS-PROFIB/AX - D-SUB bus connector



2744377

<https://www.phoenixcontact.com/us/products/2744377>

|      |   |
|------|---|
| Note | Please follow the special installation instructions in the documentation! |
|------|---|

## UKEX

|                |                          |
|----------------|--------------------------|
| Identification | Ⓜ II 3 G Ex ec IIC T4 Gc |
| Certificate    | PxCIMA22UKEX2744348X     |

## Corrosive gas test

|                |                                  |
|----------------|----------------------------------|
| Identification | ISA-S71.04-1985 G3 Harsh Group A |
|----------------|----------------------------------|

## Standards and regulations

|   |                    |
|---|--------------------|
| Free from substances that could impair the application of coating | VDMA 24364:2018-05 |
|---|--------------------|

# SUBCON-PLUS-PROFIB/AX - D-SUB bus connector




2744377

<https://www.phoenixcontact.com/us/products/2744377>

## Drawings

Dimensional drawing



Dimensional drawing


# SUBCON-PLUS-PROFIB/AX - D-SUB bus connector



2744377

<https://www.phoenixcontact.com/us/products/2744377>

Schematic diagram



Function elements


# SUBCON-PLUS-PROFIB/AX - D-SUB bus connector



2744377

<https://www.phoenixcontact.com/us/products/2744377>

Schematic diagram



Stripping specifications

# SUBCON-PLUS-PROFIB/AX - D-SUB bus connector



2744377

<https://www.phoenixcontact.com/us/products/2744377>

Circuit diagram



Functional diagram of the connector range  
SUBCON-PLUS-PROFIB/...

# SUBCON-PLUS-PROFIB/AX - D-SUB bus connector



2744377

<https://www.phoenixcontact.com/us/products/2744377>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2744377>



**cUL Recognized**  
Approval ID: E238705



**UL Recognized**  
Approval ID: E238705



**CSA**  
Approval ID: 2437602

# SUBCON-PLUS-PROFIB/AX - D-SUB bus connector



2744377

<https://www.phoenixcontact.com/us/products/2744377>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440302 |
| ECLASS-15.0 | 27440322 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001132 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SUBCON-PLUS-PROFIB/AX - D-SUB bus connector



2744377

<https://www.phoenixcontact.com/us/products/2744377>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.561 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)