

# FL PLUG RJ45 GR/2 - RJ45 connector



2744856

<https://www.phoenixcontact.com/us/products/2744856>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Plastic, connection method: Crimp connection, connection cross section: AWG 26- 24, cable outlet: straight, color: gray, Ethernet

The figure shows the version FL  
PLUG RJ45 GN/2

## Your advantages

- Set of 2 connectors
- Easy installation with a crimping tool
- With gray bend protection sleeve: recommended for straight, uncrossed cables

## Commercial data

Item number	2744856
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB10
Product key	ABNAAG
GTIN	4017918607579
Weight per piece (including packing)	18.8 g
Weight per piece (excluding packing)	6.596 g
Customs tariff number	85366990
Country of origin	US

# FL PLUG RJ45 GR/2 - RJ45 connector



2744856

<https://www.phoenixcontact.com/us/products/2744856>

## Technical data

### Product properties

Product type	Data connector (cable side)
Type	RJ45
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
Cable outlet	straight
Positions/contacts	8P8C

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Contact resistance	< 100 mΩ (max.)
Frequency range	100 MHz
Insulation resistance	> 500 MΩ
Nominal current I <sub>N</sub>	1.5 A
Contact resistance per contact pair	< 20 Ω
Contact resistance	> 10 mΩ
Transmission medium	Copper
Transmission speed	1 Gbps
Transmission characteristics (category)	CAT5
Transmission speed	1 Gbps

### Connection data

#### Connection technology

Connection method	Crimp connection
Connection cross section AWG	26 ... 24 (solid) 26 ... 24 (flexible)
Conductor cross-section	0.14 mm <sup>2</sup> ... 0.22 mm <sup>2</sup> (solid) 0.14 mm <sup>2</sup> ... 0.22 mm <sup>2</sup> (flexible)

### Dimensions

Width	13.7 mm
Height	13.1 mm
Length	32.7 mm

### Material specifications

Color	gray
Flammability rating according to UL 94	V0
Housing material	Plastic

# FL PLUG RJ45 GR/2 - RJ45 connector



2744856

<https://www.phoenixcontact.com/us/products/2744856>

Contact material	Phosphor bronze
Contact surface material	Au/Ni
Contact carrier material	PC
Locking latch material	PC

## Cable/line

External cable diameter	4.6 mm ... 5.8 mm
Cable cross section	0.14 mm <sup>2</sup>
Test voltage Core/Core	1000 V
Test voltage Core/Shield	1500.00 V

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	min. 2500
Insertion force per signal contact	< 20.00 N
Extraction force per signal contact	< 20 N

## Mounting

Mounting type	Crimp connection
---------------	------------------

# FL PLUG RJ45 GR/2 - RJ45 connector



2744856

<https://www.phoenixcontact.com/us/products/2744856>

## Classifications

### ECLASS

ECLASS-13.0	27440114
ECLASS-15.0	27440114

### ETIM

ETIM 10.0	EC002636
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FL PLUG RJ45 GR/2 - RJ45 connector



2744856

<https://www.phoenixcontact.com/us/products/2744856>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)