

UM122 PROFIL 1,15CM GN - Profile



2697673

<https://www.phoenixcontact.com/us/products/2697673>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Latching with side elements, latching with foot element, Basic profile, length: 11.5 mm



Commercial data

Item number	2697673
Packing unit	50 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	ACHDBA
GTIN	4046356009881
Weight per piece (including packing)	6.986 g
Weight per piece (excluding packing)	6.04 g
Country of origin	DE

UM122 PROFIL 1,15CM GN - Profile



2697673

<https://www.phoenixcontact.com/us/products/2697673>

Technical data

Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing type	Extruded profile housings
Housing series	UM
Product family	UM122
Ventilation openings present	no

Dimensions

Length	11.5 mm
--------	---------

Material specifications

Color (Profile)	green (RAL 6021)
Material Profile	PA
Flammability rating according to UL 94	V0
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Latching with side elements, latching with foot element
---------------	---

UM122 PROFIL 1,15CM GN - Profile



2697673

<https://www.phoenixcontact.com/us/products/2697673>

Classifications

ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM122 PROFIL 1,15CM GN - Profile



2697673

<https://www.phoenixcontact.com/us/products/2697673>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com