

# PSM-LWL/KDL - FO cable



2744953

<https://www.phoenixcontact.com/us/products/2744953>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Polymer fiber cable, duplex 980/1000  $\mu\text{m}$ , light-weight version for indoor installation, by the meter, with connector

The figure shows version PSM-LWL-KDL-980/1000

## Commercial data

Item number	2744953
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DNC241
Weight per piece (including packing)	68 g
Weight per piece (excluding packing)	68 g
Customs tariff number	85447000
Country of origin	DE

## Technical data

### Product properties

Product type	Data cable by the meter
--------------	-------------------------

### Electrical properties

Transmission medium	FO
---------------------	----

### Interfaces

Signal	PROFIBUS
	Modbus

### Dimensions

#### External dimensions

External diameter min.	2.2 mm
External diameter max.	4.4 mm

### Material specifications

Color (Single-core wire)	black (RAL 9005)
--------------------------	------------------

### Cable/line

Cable length	variable
Cable weight	7.8 kg/km
Cable type	Polymer fiber
Cable abbreviation	CA-1D2Y2P 980/1000 160A 10
Single wire, number of litz wires	2
Single wire, material	PE
Individual wire diameter	2.2 mm ±0.07 mm
Bending radius, long-term	30 mm
Bending radius short term/long term	20 mm
Tensile strength short-term/long-term	40 N / 10 N
Lateral pressure short term	60 N/cm
Lateral pressure, long-term	10 N/cm

#### FO cable

Fiber	980/1000 µm
-------	-------------

### Mechanical properties

Tensile strength short-term/long-term	40 N / 10 N
---------------------------------------	-------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Altitude	5000 m

# PSM-LWL/KDL - FO cable

2744953

<https://www.phoenixcontact.com/us/products/2744953>



## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)