

IBS UART - Master protocol chip

2746391

<https://www.phoenixcontact.com/us/products/2746391>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Protocol chip, in SOP 16 housing



Commercial data

Item number	2746391
Packing unit	45 pc
Minimum order quantity	45 pc
Sales key	DR14
Product key	DRECAA
GTIN	4017918169336
Weight per piece (including packing)	3.67 g
Weight per piece (excluding packing)	3.365 g
Customs tariff number	85423990
Country of origin	CN

IBS UART - Master protocol chip



2746391

<https://www.phoenixcontact.com/us/products/2746391>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Protocol chip
Type	SOIC16 WB (300 mil)

Electrical properties

IC power supply voltage	5 V DC \pm 10 % (DC)
-------------------------	------------------------

Supply

Typical current consumption	10 mA (all inputs static, outputs unused)
-----------------------------	---

Interfaces

INTERBUS

Connection method	Remote bus/local bus
-------------------	----------------------

User interface

Connection method	V.24, 1 start bit, 2 stop bits, 8 data bits, even parity
-------------------	--

Dimensions

Width	11 mm
Height	10 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Ambient temperature (operation)	-40 °C ... 85 °C

IBS UART - Master protocol chip

2746391

<https://www.phoenixcontact.com/us/products/2746391>



Classifications

ECLASS

ECLASS-13.0	27242605
ECLASS-15.0	27242605

ETIM

ETIM 10.0	EC001601
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

IBS UART - Master protocol chip



2746391

<https://www.phoenixcontact.com/us/products/2746391>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	1.486 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com