

# PSD-S AE BM2-1 85DB - Acoustic element



2700136

<https://www.phoenixcontact.com/us/products/2700136>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Buzzer element, continuous/pulse tone, 24 V AC/DC, max. 85 dB(A), black



## Product description

This audible signal element is designed as a component of a modular signal tower. According to your requirements, a signal tower may comprise any combination of up to five signal elements. You may use up to five optical signal elements or up to four optical and one audible signal element. Only use an audible signal element as the top element. A bayonet locking system establishes the mechanical and electrical connection between the elements. Connection elements with spring-cage or screw connection can be used for electrical connection of the signal tower. Mounting elements for base or tube mounting can be used to mount the signal tower. Please note that PSD-S signal towers (70 mm diameter) are not mechanically compatible with PSD-S 50 signal towers (50 mm diameter).

## Your advantages

- Multi-tone siren signaling depending on the situation
- Tone function can be set via DIP switches
- Degree of protection: IP65, when mounted

## Commercial data

Item number	2700136
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR07
Product key	DRL113
GTIN	4046356491280
Weight per piece (including packing)	86.8 g
Weight per piece (excluding packing)	69 g
Customs tariff number	85318070
Country of origin	DE

# PSD-S AE BM2-1 85DB - Acoustic element



2700136

<https://www.phoenixcontact.com/us/products/2700136>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties


Product type	Signal element
Product family	PSD-S

### Electrical properties

#### General

Input voltage	24 V AC/DC $\pm 10\%$
Nominal input voltage range	21.6 V AC/DC ... 26.4 V AC/DC
Maximum inrush current	max. 200 mA
Current consumption	typ. 11 mA
Operating time	100 %
Service life electrical	min. 5,000 h
Type of acoustic signal	Continuous tone Pulse tone
Signal frequency	1 Hz (Pulse tone)
Tone frequency	3.5 kHz
Volume	max. 85 dB

### Dimensions

Dimensional drawing	
Height	72 mm
Diameter	70 mm

### Material specifications

Color (Housing)	black (RAL 9005)
Material	Polycarbonate PC

### Environmental and real-life conditions

#### Ambient conditions

# PSD-S AE BM2-1 85DB - Acoustic element



2700136

<https://www.phoenixcontact.com/us/products/2700136>

Degree of protection	IP65, when installed
Ambient temperature (operation)	-30 °C ... 50 °C

## Mounting

Mounting type	Plug-in mounting
Mounting position	any

# PSD-S AE BM2-1 85DB - Acoustic element




2700136

<https://www.phoenixcontact.com/us/products/2700136>

## Drawings

Dimensional drawing



# PSD-S AE BM2-1 85DB - Acoustic element



2700136

<https://www.phoenixcontact.com/us/products/2700136>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2700136>



**cULus Listed**

Approval ID: E123528



**cULus Listed**

Approval ID: E123528

# PSD-S AE BM2-1 85DB - Acoustic element



2700136

<https://www.phoenixcontact.com/us/products/2700136>

## Classifications

### ECLASS

ECLASS-13.0	27371237
ECLASS-15.0	27371237

### ETIM

ETIM 10.0	EC001261
-----------	----------

### UNSPSC

UNSPSC 21.0	46171600
-------------	----------

# PSD-S AE BM2-1 85DB - Acoustic element



2700136

<https://www.phoenixcontact.com/us/products/2700136>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead titanium zirconium oxide(CAS: 12626-81-2)
	Lead(CAS: 7439-92-1)

### EF3.1 Climate Change

CO2e kg	4.172 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)