

IBS SAB 24 DIO 4/4/2 - Distributed I/O device



2750921

<https://www.phoenixcontact.com/us/products/2750921>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



INTERBUS sensor/actuator box, digital input/output module, 4 digital inputs, 24 V DC, 4-conductor connection technology, 2 digital outputs, 24 V DC, 2 A, 3-conductor connection technology, IP67 degree of protection

The figure shows the version
IBS SAB 24 DI 4/4

Commercial data

Item number	2750921
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRIA43
GTIN	4017918099244
Weight per piece (including packing)	340.5 g
Weight per piece (excluding packing)	340.5 g
Customs tariff number	85389091
Country of origin	DE

IBS SAB 24 DIO 4/4/2 - Distributed I/O device




2750921

<https://www.phoenixcontact.com/us/products/2750921>

Technical data

Dimensions

Dimensional drawing	
Width	61 mm
Height	77 mm
Length	132 mm

Interfaces

Installation remote bus	
Connection method	SAB connector hood with MINI-COMBICON
Transmission speed	500 kbps
Transmission physics	Copper

Input data

Digital	
Number of inputs	4
Input voltage range "0" signal	-30 V DC ... 5 V DC
Input voltage range "1" signal	13 V DC ... 30 V DC
Protective circuit	Reverse polarity protection
Connection method	5-pos. M12 sensor connector, female
Connection technology	4-conductor
Typical input current per channel	5 mA

Output data

Digital	
Number of outputs	2
Output voltage	$U_S - 1 \text{ V}$
Protective circuit	Short-circuit protection

Product properties

Product type	I/O component
Type	Stand-alone

Electrical properties

IBS SAB 24 DIO 4/4/2 - Distributed I/O device



2750921

<https://www.phoenixcontact.com/us/products/2750921>

Supply

I/O voltage	± 24 V DC 5 % (ripple)
I/O voltage range	20 V DC ... 30 V DC
Max. current consumption	500 mA (at 24 V DC (with load))
Typical current consumption	100 mA (from the installation remote bus)

Connection data

Connection method	Pg9 screw connection
Conductor cross-section, rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP66
----------------------	-----------

Mounting

Mounting type	Panel mounting
---------------	----------------


IBS SAB 24 DIO 4/4/2 - Distributed I/O device



2750921

<https://www.phoenixcontact.com/us/products/2750921>

Drawings



IBS SAB 24 DIO 4/4/2 - Distributed I/O device



2750921

<https://www.phoenixcontact.com/us/products/2750921>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com