

IBS ST 24 BKM-LK - Bus coupler



2750963

<https://www.phoenixcontact.com/us/products/2750963>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



INTERBUS-ST bus terminal module, 24 V DC, with optical fiber F-SMA connector, IP20 protection, consisting of: Terminal part with screw connection and module electronics

Product description

INTERBUS ST standard bus terminal modules

The INTERBUS bus terminal module connects the input/output modules of an ST station with the INTERBUS network.

Depending on the transmission medium used, the bus terminal modules are equipped with different bus connections. For copper conductors, D-SUB and MINI-COMBICON connectors are available. The fiber optic versions are equipped with F-SMA connectors.

The bus terminal modules are available in two different performance classes. A maximum of 4 or 8 input/output modules can be operated on one bus terminal module.

The bus terminal module takes on the following functions within a modular INTERBUS-ST station:

- Refreshing the INTERBUS remote bus signals
- Electrical isolation of the remote bus segments
- Decoupling of the outgoing remote bus or of the connected input/ output modules from the INTERBUS network with a software command
- Supply of the connected input/output modules with an electrically isolated voltage supply from an integrated power supply unit

Commercial data

Item number	2750963
Packing unit	1 pc
Sales key	NULL
Product key	DRI311
GTIN	4017918120160
Weight per piece (including packing)	256.2 g
Weight per piece (excluding packing)	166.18 g
Customs tariff number	85389091
Country of origin	DE


IBS ST 24 BKM-LK - Bus coupler

2750963

<https://www.phoenixcontact.com/us/products/2750963>

Technical data

Dimensions

Dimensional drawing	
Width	44 mm
Height	117 mm
Length	116 mm

Interfaces

INTERBUS remote bus (incoming/outgoing)

Connection method	4x F-SMA connector
Transmission speed	500 kbps

ST local bus

Connection method	ST local bus connector
Transmission speed	500 kbps

Product properties

Product type	I/O component
Product family	Smart Terminal ST
Type	modular

Electrical properties

Test section	Between supply voltage and ST local bus 500 V AC 50 Hz 1 min
--------------	--

Supply

I/O voltage	24 V DC
I/O voltage range	20 V DC ... 30 V DC
Residual ripple	± 1.2 V
Max. current consumption	300 mA (for max. terminal configuration) 500 mA (of all I/O modules max.)
Typical current consumption	70 mA (without connected ST I/O modules)

Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

IBS ST 24 BKM-LK - Bus coupler



2750963

<https://www.phoenixcontact.com/us/products/2750963>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
----------------------	------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IBS ST 24 BKM-LK - Bus coupler


2750963

<https://www.phoenixcontact.com/us/products/2750963>



Drawings

Dimensional drawing




IBS ST 24 BKM-LK - Bus coupler

2750963

<https://www.phoenixcontact.com/us/products/2750963>



Connection diagram



IBS ST 24 BKM-LK - Bus coupler

2750963

<https://www.phoenixcontact.com/us/products/2750963>



Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com