

IBS UNI DIO - Plug-in board



2753672

<https://www.phoenixcontact.com/us/products/2753672>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in board, Daughterboard, INTERBUS, Interface implementation, 10 bytes IN and 10 bytes OUT data, 60-pos. female connector for power supply, -Diagnostics, -Configuration, -Parallel port for 32 data bits (configurable), -Parallel port for micro-processor

Commercial data

Item number	2753672
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR14
Product key	DRECAA
GTIN	4017918153526
Weight per piece (including packing)	36 g
Weight per piece (excluding packing)	20 g
Customs tariff number	85389091
Country of origin	DE

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Plug-in board
Type	Daughterboard

System properties

Module

Internal data length	10 bytes IN and 10 bytes OUT data
Protocol chip	INTERBUS SUPI 3

Electrical properties

IC power supply voltage	5 V DC \pm 10 % (DC)
-------------------------	------------------------

Supply

Typical current consumption	120 mA (90 mA kernel)
-----------------------------	-----------------------

Interfaces

User interface	60-pos. female connector for power supply, -Diagnostics, - Configuration, -Parallel port for 32 data bits (configurable), - Parallel port for micro-processor
----------------	---

INTERBUS

Connection method	Remote bus
-------------------	------------

Dimensions

Width	70 mm
Height	10 mm
Length	50 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Ambient temperature (operation)	0 °C ... 70 °C

IBS UNI DIO - Plug-in board

2753672

<https://www.phoenixcontact.com/us/products/2753672>



Classifications

ECLASS

ECLASS-13.0	27242605
ECLASS-15.0	27242605

ETIM

ETIM 10.0	EC001601
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	2.816 kg CO2e
---------	---------------