

FL WLAN 230 AP 802-11-US - Wireless module



2700452

<https://www.phoenixcontact.com/us/products/2700452>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



WLAN access point for the USA and Canada, 110/230 V AC, IEEE 802.11 a/b/g; 2.4 GHz; 5 GHz, client adapter; antenna diversity; web-based management; 802.11i, WPA2, WPA-PSK, RADIUS, WEP, TKIP, AES

Your advantages

- 2.4 GHz and 5 GHz supported
- High resistance to vibration, shock, and EMI
- Maximum security according to IEEE 802.11i with AES encryption
- Range of several hundred meters*

Commercial data

Item number	2700452
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN26
Product key	DNN2W1
GTIN	4046356553056
Weight per piece (including packing)	1.3 kg
Weight per piece (excluding packing)	1.3 kg
Customs tariff number	85176200
Country of origin	DE

2700452

<https://www.phoenixcontact.com/us/products/2700452>

Technical data

Product properties

Product type	Wireless module
Type	Stand-alone

Wireless card

Number	1
Type	IEEE 802.11a/b/g, 2.4 and 5 GHz to 54 Mbps
Assembly note	Permanently installed

Electrical properties

Maximum power dissipation for nominal condition	9.6 W
---	-------

Supply: Module electronics

Connection method	Via COMBICON
Supply voltage	110 V AC (PoE)
Supply voltage range	110 V AC ... 230 V AC
Supply current	400 mA (Recommended protection 2AT)

Interfaces

Ethernet

Interface	Ethernet
Number	1
Connection method	RJ45 jack

Antenna

Number	2
Connection method	RSMA (male)

Functions

Operating modes	Access Point
Configuration	Multilingual web-based interface (German/English) under http or https, with password protection
Automatic channel selection	yes
Quality of service (QoS)	Yes
Virtual LAN (VLAN) support 802.1Q	yes
Security	WEP 64 bit/128 bit
	WEPplus
	WPA TKIP
	802.11i WPA2 (RSN,AES)
	WPA PSK (preshared key)
	WPA group & master rekeying
Country support	USA
	Canada

FL WLAN 230 AP 802-11-US - Wireless module



2700452

<https://www.phoenixcontact.com/us/products/2700452>

Wireless

Designation	Wireless card
Antenna connection method	RSMA (female)
Frequency band	2.4 GHz
	5 GHz
Wireless standard	WLAN
	IEEE 802.11
	a
	b
	g
	h
Transmission power	20 dBm (EIRP)
Number of wireless interfaces	1 IEEE 802.11 a/b/g
Wireless modules that can be connected	256 (More than)

Dimensions

Width	159 mm
Height	250 mm
Depth	65 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-20 °C ... 55 °C
Air pressure (operation)	795 hPa ... 1080 hPa (up to 2000 m above sea level)
Permissible humidity (operation)	10 % ... 85 % (non-condensing)

Mechanical test

Shock in accordance with EN 60068-2-27/IEC 60068-2-27	25g
Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	5g

Standards and regulations

Protection class	I (IEC 61140, EN 61140, VDE 0140-1)
------------------	-------------------------------------

Mounting

Mounting type	Adapter plate
	Panel mounting on adapter plate
Assembly note	External OMNI omnidirectional antenna, the antennas can be exchanged

FL WLAN 230 AP 802-11-US - Wireless module



2700452

<https://www.phoenixcontact.com/us/products/2700452>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com