

# NLC-055-024D-08I-04QTP-00A - Base unit



2700453

<https://www.phoenixcontact.com/us/products/2700453>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



24 V DC Nanoline base unit. Equipped with 8 digital inputs, 2 analog (0-10 V) inputs and 4 PNP digital output channels. Additional I/O channels can be added using a maximum of three I/O extension modules. Optional communication modules provide network or serial connectivity. Optional Operator Panel provides user interface. Programming is via nanoNavigator.

## Commercial data

Item number	2700453
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR11
Product key	DRACAA
GTIN	4046356646536
Weight per piece (including packing)	335.6 g
Weight per piece (excluding packing)	321.5 g
Customs tariff number	85371098
Country of origin	IN

## Technical data

### Product properties

Product type	Base unit
Product family	Nanoline

### Electrical properties

#### Supply

Supply voltage	24 V DC (Power available to the I/O and Communications modules)
Supply voltage range	19.2 V DC ... 30 V DC
Power supply connection	Screw connection
Max. current consumption	250 mA
Typical current consumption	100 mA

#### Real-time clock

Realtime clock	Yes (battery-backed)
Description realtime clock	±2 s/day @ 25°C ±4 s/day @ -20 °C ... +60 °C Lithium BR2330

### Input data

#### Analog:

Description of the input	Analog input
Number of inputs	2
Connection technology	Screw connection
Voltage input signal	0 V DC ... 10 V DC
Input resistance of voltage input	20 kΩ
A/D converter resolution	12 bit (monotonic)
Input filter	digital
Limit frequency (3 dB)	1 Hz (3 dB)
Measuring principle	Successive approximation
Protective circuit	Transient voltage suppression

#### Digital:

Input name	Digital inputs
Description of the input	EN 61131-2 type 1 NPN/PNP
Number of inputs	8
Connection method	Screw connection
Input voltage range "0" signal	0 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Nominal input voltage $U_{IN}$	24 V DC
Nominal input current at $U_{IN}$	5 mA DC (On) < 100 mA (Off)
Typical response time	60 μs (on) 70 μs (OFF)

2700453

<https://www.phoenixcontact.com/us/products/2700453>

## Counter:

Number of inputs	2
Input frequency	6 kHz

## Output data

### Digital:

Output name	Digital outputs
Output description	PNP outputs
Connection method	Screw connection
Number of outputs	4
Protective circuit	Short-circuit and overload protection
Maximum output current per channel	500 mA
Maximum output current per module / terminal block	2 A
Nominal output voltage	24 V DC
Nominal load, inductive	12 VA
Nominal load, lamp	12 W
Nominal load, ohmic	12 W
Maximum operating frequency with ohmic nominal load	100 Hz

## Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

## Interfaces

### Operator Panel

Connection method	RJ45 / COMBICON
-------------------	-----------------


### RS-232

Connection method	Slot 1
-------------------	--------

### USB

Connection method	Slot 1
-------------------	--------

## Dimensions

Dimensional drawing	
Width	80.5 mm
Height	103.5 mm

2700453

<https://www.phoenixcontact.com/us/products/2700453>

Depth	60 mm
-------	-------

## Material specifications

Color	white
-------	-------

## Environmental and real-life conditions

### Ambient conditions


Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	90 %
Permissible humidity (storage/transport)	90 %

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Drawings

Dimensional drawing



2700453

<https://www.phoenixcontact.com/us/products/2700453>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2700453>



**UL Listed**

Approval ID: E238705



**cUL Listed**

Approval ID: E238705

2700453

<https://www.phoenixcontact.com/us/products/2700453>

## Classifications

### ECLASS

ECLASS-13.0

27242216

### ETIM

ETIM 9.0

EC001417

### UNSPSC

UNSPSC 21.0

39122300

2700453

<https://www.phoenixcontact.com/us/products/2700453>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	1, 2-dimethoxyethane; ethylene glycol dimethyl ether (EGDME)(CAS: 110-71-4)
	Lead(CAS: 7439-92-1)
SCIP	4956f986-b7c6-44ea-9943-85ae028ad01b

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
 586 Fulling Mill Road  
 Middletown, PA 17057, United States  
 (+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)