


# IB IL AI 4/U-PAC - Analog module

2700459

<https://www.phoenixcontact.com/us/products/2700459>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Analog input terminal, Analog inputs: 4, 0 V ... 10 V, -10 V ... 10 V, connection technology: 2-conductor, transmission speed in the local bus: 500 kbps, degree of protection: IP20, including Inline connector and labeling field

The figure shows version: IB IL AI 4/I-PAC

## Your advantages

- 4 analog, bipolar input channels for the connection of voltage signals
- Connection of sensors in 2-conductor technology
- Voltage ranges: 0 V ... 10 V,  $\pm 10$  V
- Mean value generation of the inputs
- Process data update of all channels in 250  $\mu$ s
- Diagnostic and status indicators

## Commercial data

Item number	2700459
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI141
GTIN	4046356566537
Weight per piece (including packing)	90 g
Weight per piece (excluding packing)	88 g
Customs tariff number	85389091
Country of origin	DE

## Technical data

### Dimensions

Dimensional drawing	
Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

### Interfaces

#### Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps
Transmission physics	Copper

### System properties

#### Programming data (LocalbusSlave)

Length code (hex)	04
ID code (dec.)	127
Length code (dec)	04
Process data channel	64 bit
Input address area	8 Byte
Output address area	8 Byte
Parameter channel (PCP)	0 Byte
Register length (bus)	64 bit

#### Fieldbus data telegram (PROFIBUS)

Required parameter data	10 Byte
Required configuration data	5 Byte

# IB IL AI 4/U-PAC - Analog module



2700459

<https://www.phoenixcontact.com/us/products/2700459>

## Input data

### Analog:

Input name	Analog inputs
Description of the input	Differential inputs, voltage
Number of inputs	4
A/D conversion time	max. 6.5 $\mu$ s
Connection method	Inline connector
Connection technology	2-conductor
Voltage input signal	0 V ... 10 V -10 V ... 10 V
Input resistance of voltage input	typ. 324 k $\Omega$
A/D converter resolution	12 bit
Data formats	IB IL, S7-compatible
Filtering	None or mean value generation over 4, 16, or 32 measured values
Limit frequency (3 dB)	300 Hz
Common mode voltage range signal - ground	max. 50 V
Measured value resolution	12 bits (11 bits + sign bit)
Measured value representation	12 bits (11 bits + sign bit)
Protective circuit	Overload protection; $\pm$ 30 V DC, maximum

## Product properties

Product type	I/O component
Product family	Inline
Type	modular
Installation location	Control cabinet
Scope of supply	including Inline connector and labeling field
Diagnostics messages	Failure of the internal I/O supply I/O error message sent to the bus coupler I/O supply failure Message in the diagnostic code (in the IB IL format) Overrange or underrange Message in the diagnostic code (in the IB IL format) Configuration invalid Message in the diagnostic code (in the IB IL format)

### Insulation characteristics

Overvoltage category	II (IEC 60664-1, EN 60664-1)
Pollution degree	2 (IEC 60664-1, EN 60664-1)

## Electrical properties

Maximum power dissipation for nominal condition	1.25 W
---	--------

### Potentials: Communications power ( $U_L$ )

Supply voltage	7.5 V DC (via voltage jumper)
----------------	-------------------------------

# IB IL AI 4/U-PAC - Analog module



2700459

<https://www.phoenixcontact.com/us/products/2700459>

Current draw	max. 60 mA
	typ. 55 mA

## Potentials: Supply of analog modules ( $U_{ANA}$ )

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 35 mA
	typ. 30 mA

## Electrical isolation/isolation of the voltage ranges

Test voltage: 7.5 V supply (bus logic), 24 V supply $U_{ANA}$ / I/O	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logic), 24 V supply $U_{ANA}$ / functional ground	500 V AC, 50 Hz, 1 min
Test voltage: I/O/functional ground	500 V AC, 50 Hz, 1 min

## Connection data

### Connection technology

Connection name	Inline connector
-----------------	------------------

### Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

### Mechanical test

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	5g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	25g

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IB IL AI 4/U-PAC - Analog module

2700459


<https://www.phoenixcontact.com/us/products/2700459>

## Drawings

Dimensional drawing



Connection diagram



# IB IL AI 4/U-PAC - Analog module



2700459

<https://www.phoenixcontact.com/us/products/2700459>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2700459>



**cULus Listed**

Approval ID: E140324



**cULus Listed**

Approval ID: E140324

# IB IL AI 4/U-PAC - Analog module



2700459

<https://www.phoenixcontact.com/us/products/2700459>

## Classifications

### ECLASS

ECLASS-13.0	27242601
ECLASS-15.0	27242601

### ETIM

ETIM 10.0	EC001596
-----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

# IB IL AI 4/U-PAC - Analog module



2700459

<https://www.phoenixcontact.com/us/products/2700459>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	8c65eeb1-0f7b-4951-a887-86d3da55f0f7

### EF3.1 Climate Change

CO2e kg	6.513 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)