

IB IL 24 PSDOR 4-F-PAC - Safety module



2700563

<https://www.phoenixcontact.com/us/products/2700563>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shows the IB IL PSDOR 4-PAC version

Safety-related distributed relay output module, IP20 protection, for the PROFIsafe system. The module has 4 safe relay outputs, each with two contacts. The output states are mirrored for diagnostic purposes.

Product description

The safety module is an output module from the Inline product range, designed for use in a PROFIsafe system. The safety module can be used as part of an Inline station at any point within a PROFIsafe Inline system. The transmission speed can be set to 500 kbaud or 2 Mbaud on the safety module using a switch. One transmission speed must be used consistently within a station. The module has four safe relay outputs, each with two relay contacts. The output states are mirrored for diagnostic purposes.

Your advantages

- SIL 3 in accordance with EN IEC 62061
- SIL 3 according to IEC/EN 61508
- PL e in accordance with EN ISO 13849-1

Commercial data

Item number	2700563
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DNA432
GTIN	4046356583169
Weight per piece (including packing)	449.2 g
Weight per piece (excluding packing)	449.2 g
Country of origin	DE

Technical data

Dimensions

Width	73.2 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Material specifications

Color (Housing)	yellow (RAL 1018)
-----------------	-------------------

Interfaces

Inline local bus

No. of channels	2
Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps (can be switched)

System properties

Programming data

Length code (hex)	04
ID code (dec.)	175
Length code (dec)	04

Output data

Relay

Number of outputs	4 (Safety relays with 2 floating contacts each)
Connection method	Spring-cage connection
Contact switching type	N/O contact

Product properties

Product type	I/O component
Product family	Inline
Application	Functional safety PROFIsafe
Type	modular

Electrical properties

Maximum power dissipation for nominal condition	8.7 W
---	-------

IB IL 24 PSDOR 4-F-PAC - Safety module



2700563

<https://www.phoenixcontact.com/us/products/2700563>

Transmission medium	Copper
Potentials: Communications power (U_L)	
Supply voltage	7.5 V DC (see safety data)
Current draw	max. 360 mA
Potentials: Main circuit supply (U_M)	
Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including ripple)
Current draw	typ. 30 mA
Potentials: Segment circuit supply (U_S)	
Supply voltage	24 V
Supply: Module electronics	
Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC
Electrical isolation/isolation of the voltage ranges	
Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logic)/24 V supply (U_M , U_S), GND, clock outputs, relay outputs, FE	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply (U_M , U_S), GND, clock outputs/7.5 V supply (bus logic), relay outputs	500 V AC, 50 Hz, 1 min
Test voltage: COMBICON X3 relay outputs/COMBICON X4 relay outputs, Inline connector relay outputs, 7.5 V supply (bus logic), 24 V supply (U_M , U_S), GND, clock outputs, FE	2500 V AC, 50 Hz, 1 min
Test voltage: COMBICON X4 relay outputs/COMBICON X3 relay outputs, Inline connector relay outputs, 7.5 V supply (bus logic), 24 V supply (U_M , U_S), GND, clock outputs,	2500 V AC, 50 Hz, 1 min

Connection data

Connection technology

Connection name	Inline connector
pluggable	yes

Inline connector

Connection method	Spring-cage connection
pluggable	yes
Conductor cross-section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16

Environmental and real-life conditions

Ambient conditions

IB IL 24 PSDOR 4-F-PAC - Safety module



2700563

<https://www.phoenixcontact.com/us/products/2700563>

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	80 kPa ... 108 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)
Permissible humidity (storage/transport)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)

Standards and regulations

Protection class	I (IEC 61140, EN 61140, VDE 0140-1)
------------------	-------------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL 24 PSDOR 4-F-PAC - Safety module



2700563

<https://www.phoenixcontact.com/us/products/2700563>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2700563>

PROFIsafe
Approval ID: Z20083

2700563

<https://www.phoenixcontact.com/us/products/2700563>

Classifications

ECLASS

ECLASS-13.0	27242604
ECLASS-15.0	27242604
ECLASS-15.0 ASSET	27250101

ETIM

ETIM 10.0	EC001599
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

2700563

<https://www.phoenixcontact.com/us/products/2700563>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a9bc7f19-379d-47ec-b007-05f3863bb403

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com