

# UKKB 10 - Double-level terminal block



2772077

<https://www.phoenixcontact.com/us/products/2772077>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Double-level terminal block, nom. voltage: 500 V, nominal current: 57 A, connection method: Screw connection, 1st and 2nd level, Rated cross section: 10 mm<sup>2</sup>, cross section: 0.5 mm<sup>2</sup> - 16 mm<sup>2</sup>, Rated cross section: 10 mm<sup>2</sup>, cross section: 0.5 mm<sup>2</sup> - 16 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, NS 32, color: gray

## Your advantages

- Design width of just 10.2 mm

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2772077       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE12          |
| Product key                          | BE1214        |
| GTIN                                 | 4017918068240 |
| Weight per piece (including packing) | 43.86 g       |
| Weight per piece (excluding packing) | 43.86 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | TR            |

# UKKB 10 - Double-level terminal block



2772077

<https://www.phoenixcontact.com/us/products/2772077>

## Technical data

### Product properties

|                       |                            |
|-----------------------|----------------------------|
| Product type          | Multi-level terminal block |
| Product family        | UK                         |
| Number of connections | 4                          |
| Number of rows        | 2                          |
| Potentials            | 2                          |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 6 kV   |
| Maximum power dissipation for nominal condition | 1.82 W |

### Connection data

|                                 |                    |
|---------------------------------|--------------------|
| Number of connections per level | 2                  |
| Nominal cross section           | 10 mm <sup>2</sup> |

### 1st and 2nd level

|   |  |
|---|--|
| Connection method   | Screw connection                                       |
| Screw thread  | M4   |
| Tightening torque   | 1.5 ... 1.8 Nm   |
| Stripping length  | 11 mm  |
| Internal cylindrical gage   | B6   |
| Connection in acc. with standard  | IEC 60947-7-1  |
| Conductor cross-section rigid   | 0.5 mm <sup>2</sup> ... 16 mm <sup>2</sup>             |
| Cross section AWG   | 20 ... 6 (converted acc. to IEC)                       |
| Conductor cross-section flexible  | 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>             |
| Conductor cross-section, flexible [AWG]   | 20 ... 8 (converted acc. to IEC)                       |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>             |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>              |
| 2 conductors with same cross section, rigid   | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>              |
| 2 conductors with same cross section, flexible  | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>              |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>              |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>              |
| Nominal cross section   | 10 mm <sup>2</sup>                                     |
| Nominal current   | 57 A   |
| Maximum load current  | 76 A (with 16 mm <sup>2</sup> conductor cross-section) |
| Nominal voltage   | 500 V  |
| Screw thread  | M4   |

# UKKB 10 - Double-level terminal block



2772077

<https://www.phoenixcontact.com/us/products/2772077>

|   |  |
|---|--|
| Tightening torque   | 1.5 ... 1.8 Nm   |
| Stripping length  | 11 mm  |
| Connection in acc. with standard  | IEC 60947-7-1  |
| Conductor cross-section rigid   | 0.5 mm <sup>2</sup> ... 16 mm <sup>2</sup>             |
| Cross section AWG   | 20 ... 6 (converted acc. to IEC)                       |
| Conductor cross-section flexible  | 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>             |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>             |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>              |
| 2 conductors with same cross section, rigid   | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>              |
| 2 conductors with same cross section, flexible  | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>              |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>              |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>              |
| Nominal cross section   | 10 mm <sup>2</sup>                                     |
| Nominal current   | 57 A   |
| Maximum load current  | 76 A (with 16 mm <sup>2</sup> conductor cross-section) |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 10.2 mm |
| End cover width    | 1.5 mm  |
| Height             | 77.5 mm |
| Depth on NS 32     | 78 mm   |
| Depth on NS 35/7,5 | 73 mm   |
| Depth on NS 35/15  | 80.5 mm |

## Material specifications

|   |                 |
|---|-----------------|
| Color   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material group   | I               |
| Insulating material   | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Electrical tests

# UKKB 10 - Double-level terminal block



2772077

<https://www.phoenixcontact.com/us/products/2772077>

## Surge voltage test

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 7.3 kV      |
| Result                | Test passed |

## Temperature-rise test

|   |                                     |
|---|-------------------------------------|
| Requirement temperature-rise test               | Increase in temperature $\leq 45$ K |
| Result  | Test passed                         |
| Short-time withstand current 10 mm <sup>2</sup> | 1.2 kA                              |
| Short-time withstand current 16 mm <sup>2</sup> | 1.92 kA                             |
| Result  | Test passed                         |

## Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 1.89 kV     |
| Result                | Test passed |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Mechanical tests

### Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

### Attachment on the carrier

|                         |             |
|-------------------------|-------------|
| DIN rail/fixing support | NS 32/NS 35 |
| Test force setpoint     | 5 N         |
| Result                  | Test passed |

### Test for conductor damage and slackening

|                                |                              |
|--------------------------------|------------------------------|
| Rotation speed                 | 10 rpm                       |
| Revolutions                    | 135                          |
| Conductor cross-section/weight | 0.5 mm <sup>2</sup> / 0.3 kg |
|                                | 10 mm <sup>2</sup> / 2 kg    |
|                                | 16 mm <sup>2</sup> / 2.9 kg  |
| Result                         | Test passed                  |

## Environmental and real-life conditions

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Ambient conditions

|                                 |  |
|---------------------------------|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
|---------------------------------|--|

# UKKB 10 - Double-level terminal block



2772077

<https://www.phoenixcontact.com/us/products/2772077>

|  |   |
|--|---|
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C   |
| Ambient temperature (actuation)          | -5 °C ... 70 °C   |
| Permissible humidity (operation)         | 20 % ... 90 %   |
| Permissible humidity (storage/transport) | 30 % ... 70 %   |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|                                  | IEC 60947-7-1 |

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |
|               | NS 32     |

# UKKB 10 - Double-level terminal block

2772077

<https://www.phoenixcontact.com/us/products/2772077>

## Drawings

Circuit diagram



# UKKB 10 - Double-level terminal block





2772077

<https://www.phoenixcontact.com/us/products/2772077>


## Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2772077>

|  <b>CSA</b><br>Approval ID: 13631 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine  |                       |                       |                   |                      |
|  | 300 V                 | 65 A                  | 24 - 6            | -                    |

|  <b>IECEE CB Scheme</b><br>Approval ID: NL-39732 |                       |                       |                   |                      |
|---|-----------------------|-----------------------|-------------------|----------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine   |                       |                       |                   |                      |
|   | 500 V                 | -                     | -                 | - 10                 |

|  <b>EAC</b><br>Approval ID: KZ7500651131219505 |  |  |  |  |
|---|--|--|--|--|
|---|--|--|--|--|

|  <b>KEMA-KEUR</b><br>Approval ID: 71-126336 REV.1 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine  |                       |                       |                   |                      |
|  | 500 V                 | -                     | -                 | 0.5 - 10             |

|  <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| B  |                       |                       |                   |                      |
|  | 300 V                 | 65 A                  | 24 - 6            | -                    |
| C  |                       |                       |                   |                      |
|  | 300 V                 | 65 A                  | 24 - 6            | -                    |
| F  |                       |                       |                   |                      |
|  | 500 V                 | 65 A                  | 24 - 6            | -                    |
| D  |                       |                       |                   |                      |
|  | 600 V                 | 5 A                   | 24 - 6            | -                    |

# UKKB 10 - Double-level terminal block



2772077

<https://www.phoenixcontact.com/us/products/2772077>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250102 |
| ECLASS-15.0 | 27250102 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000897 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UKKB 10 - Double-level terminal block



2772077

<https://www.phoenixcontact.com/us/products/2772077>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |              |
|---------|--------------|
| CO2e kg | 0.35 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)