

IB IL 24 PSDO 8-PLSET/CP/R - Connector set



2700722

<https://www.phoenixcontact.com/us/products/2700722>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Connector set, consisting of four Inline plugs with integrated discharge electronics



Product description

Connector set, consisting of four Inline plugs with integrated discharge electronics.

It optimizes the diagnostic options and fault detection of your safety application in the case of operating external capacitive loads or cable capacitances at PSDO outputs.

When using this connector set, the typical discharge time (t_{off}) at 3.3 $\mu\text{F}/24\text{ V}$ is reduced to approx. 400 μs (30 V, t_{off} approx. 600 μs) per channel.

Your advantages

- Up to 2.2 μF per output can be connected

Commercial data

Item number	2700722
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN03
Product key	DNA43Z
GTIN	4046356651370
Weight per piece (including packing)	119 g
Weight per piece (excluding packing)	119 g
Customs tariff number	85389091
Country of origin	DE

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Connector set
Application	Inline terminals
	Functional safety

Connection data

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16

Dimensions

Width	12.2 mm
Height	138 mm
Depth	34 mm
Note on dimensions	for each connector

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Air pressure (operation)	80 kPa ... 108 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)
Permissible humidity (storage/transport)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

IB IL 24 PSDO 8-PLSET/CP/R - Connector set



2700722

<https://www.phoenixcontact.com/us/products/2700722>

Classifications

ECLASS

ECLASS-13.0	27242692
ECLASS-15.0	27242692

ETIM

ETIM 10.0	EC002584
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

2700722

<https://www.phoenixcontact.com/us/products/2700722>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)

EF3.1 Climate Change

CO2e kg	0.037 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com