

# FL SNMP OPC SERVER V3 - Driver and interface software



2701139

<https://www.phoenixcontact.com/us/products/2701139>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SNMP-OPC server, German and English, for monitoring and configuration of SNMP-capable equipment in HMI and SCADA systems

## Your advantages

- Freely configurable alarm conditions
- Any number of SNMP trap receivers can be configured

## Commercial data

Item number	2701139
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN21
Product key	DNN155
GTIN	4046356713184
Weight per piece (including packing)	81 g
Weight per piece (excluding packing)	81 g
Customs tariff number	85234910
Country of origin	DE

# FL SNMP OPC SERVER V3 - Driver and interface software



2701139

<https://www.phoenixcontact.com/us/products/2701139>

## Technical data

### Product properties

Product type	Drivers and interfaces
Scope of supply	CD-ROM with German and English product version and online documentation

### System properties

Intended use for the software	Configuration
	Diagnostics

### Functionality

Basic functions	Monitoring and configuration of 100 SNMP-compatible devices in HMI/SCADA systems
	Network monitoring with HMI/SCADA systems
	SNMP Version v1 and v2c supported
	OPC clients OPC Data Access 1.0A/2.0 or OPC Alarm and Events supported
	Integrated MIB browser
Expanded functionality	Import/export and creation of device profiles supported, online and remote configuration possible via remote PCs
Expanded functionality	The SNMP OPC server V3 is designed for a maximum of 100 devices. If additional devices are required, an extension license (Item No. 2700138) is available.
Associated hardware	Ethernet infrastructure components
Supported controllers	Ethernet infrastructure components
Number of I/O nodes	not relevant

### System requirements

Operating equipment	Keyboard, mouse recommended
Operating system	Windows® XP (SP3)
	Windows® 7
	Windows® 10
	Windows® Server 2008
	Windows® Server 2003
Processor	PC Pentium > 266 MHz
Hard disk memory	min. 20 Mbyte
Languages supported	German, English
Optical drive	CD-ROM


# FL SNMP OPC SERVER V3 - Driver and interface software

2701139

<https://www.phoenixcontact.com/us/products/2701139>

## Drawings

Block diagram



# FL SNMP OPC SERVER V3 - Driver and interface software



2701139

<https://www.phoenixcontact.com/us/products/2701139>

## Classifications

### UNSPSC

UNSPSC 21.0	43232900
-------------	----------

# FL SNMP OPC SERVER V3 - Driver and interface software



2701139

<https://www.phoenixcontact.com/us/products/2701139>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)