

NLC-OP1-MKT - Mounting kit



2701140

<https://www.phoenixcontact.com/us/products/2701140>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting kit



Product description

Mounting kit for Nanoline Operator Panel. Includes receptor housing installed in base unit, mounting brackets for installation in cabinet and cable to connect base unit.

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2701140 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | DR11 |
| Product key | DRACAZ |
| GTIN | 4046356325271 |
| Weight per piece (including packing) | 156 g |
| Weight per piece (excluding packing) | 151.6 g |
| Customs tariff number | 85366990 |
| Country of origin | IN |

NLC-OP1-MKT - Mounting kit

2701140

<https://www.phoenixcontact.com/us/products/2701140>



Set consists of

NLC-OP1-MKT-BASE - Mounting unit

2701250

<https://www.phoenixcontact.com/us/products/2701250>

Panel to mount in base unit, RJ-45 connector for remote Operator Panel



NLC-OP1-MKT-BRACKET - Mounting bracket

2701263

<https://www.phoenixcontact.com/us/products/2701263>

Mounting bracket for remote installation of Operator Panel



NLC-OP1-MKT - Mounting kit

2701140

<https://www.phoenixcontact.com/us/products/2701140>



NLC-OP1-MKT-CBL - Cable

2701438

<https://www.phoenixcontact.com/us/products/2701438>

Cable for operator terminal



NLC-OP1-MKT - Mounting kit



2701140

<https://www.phoenixcontact.com/us/products/2701140>

Technical data

Product properties

| | |
|--------------|-------------------|
| Product type | Mounting material |
|--------------|-------------------|

Electrical properties

Supply

| | |
|-----------------------------|-------|
| Max. current consumption | 50 mA |
| Typical current consumption | 32 mA |

Dimensions

| | |
|--------|---------|
| Width | 76 mm |
| Height | 31.5 mm |
| Depth | 46 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|---|----------------|
| Ambient temperature (operation) | 0 °C ... 50 °C |
| Ambient temperature (storage/transport) | 0 °C ... 60 °C |

Mounting

| | |
|---------------|-------------------------------|
| Mounting type | Control cabinet door mounting |
|---------------|-------------------------------|

NLC-OP1-MKT - Mounting kit


2701140

<https://www.phoenixcontact.com/us/products/2701140>



Drawings

Schematic diagram



NLC-OP1-MKT - Mounting kit



2701140

<https://www.phoenixcontact.com/us/products/2701140>

Classifications

ECLASS

ECLASS-13.0

27240692

ETIM

ETIM 9.0

EC002584

UNSPSC

UNSPSC 21.0

39121400

NLC-OP1-MKT - Mounting kit



2701140

<https://www.phoenixcontact.com/us/products/2701140>

Environmental product compliance

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com