

NLC-MOD-MEM 032K - Memory modul



2701166

<https://www.phoenixcontact.com/us/products/2701166>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Memory module



Your advantages

- Allows the transfer of projects from a PC to one or more Nanoline controllers without a direct connection
- Allows the transfer of projects from one controller to another without a direct connection
- Allows the transfer of a project from a controller to a replacement controller

Commercial data

Item number	2701166
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR11
Product key	DRACAD
GTIN	4046356324656
Weight per piece (including packing)	48 g
Weight per piece (excluding packing)	45.6 g
Customs tariff number	85389099
Country of origin	IN

Technical data

Product properties

Product type	Extension module
--------------	------------------

System properties

Flash memory	32 kByte
Memory type	FLASH-EPROM 32 kByte

Electrical properties

Supply

Supply voltage	Power available via logic module
Max. current consumption	20 mA
Typical current consumption	15 mA

Connection data

Slot 1

Connection method	Installs in slot 1 of logic module
-------------------	------------------------------------

Dimensions

Width	24.5 mm
Height	25.5 mm
Depth	49 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C

NLC-MOD-MEM 032K - Memory modul



2701166

<https://www.phoenixcontact.com/us/products/2701166>

Classifications

ECLASS

ECLASS-13.0

27242216

ETIM

ETIM 9.0

EC001417

UNSPSC

UNSPSC 21.0

39122300

2701166

<https://www.phoenixcontact.com/us/products/2701166>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com