


UDK 4-MTK-P/P MIT SPERRE - Knife-disconnect terminal block



2776044

<https://www.phoenixcontact.com/us/products/2776044>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Knife-disconnect terminal block, With test socket screws for insertion of test plugs, nom. voltage: 630 V, nominal current: 16 A, 1 level, connection method: Screw connection, Rated cross section: 4 mm², cross section: 0.2 mm² - 6 mm², mounting: NS 35/7,5, NS 35/15, NS 32, color: gray

Your advantages

- Space-saving design just 6.2 mm wide
- Closed housing of double-level terminal blocks
- User-friendly disconnect knife operation

Commercial data

Item number	2776044
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE12
Product key	BE1231
GTIN	4017918947644
Weight per piece (including packing)	16.52 g
Weight per piece (excluding packing)	16.46 g
Customs tariff number	85369010
Country of origin	PL

UDK 4-MTK-P/P MIT SPERRE - Knife-disconnect terminal block



2776044

<https://www.phoenixcontact.com/us/products/2776044>

Technical data

Product properties

Product type	Disconnect terminal block
Number of connections	4
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.02 W

Connection data

Number of connections per level	4
Nominal cross section	4 mm ²

1 level

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.6 ... 0.8 Nm
Stripping length	8 mm
Internal cylindrical gage	A4
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	0.2 mm ² ... 6 mm ²
Cross section AWG	24 ... 10 (converted acc. to IEC)
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Conductor cross-section, flexible [AWG]	24 ... 12 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.25 mm ² ... 4 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.25 mm ² ... 1.5 mm ²
Cross-section with insertion bridge, rigid	2.5 mm ²
Cross-section with insertion bridge, flexible	2.5 mm ²
Nominal cross section	4 mm ²
Nominal current	16 A (with 6 mm ² conductor cross-section)
Maximum load current	16 A (with a 6 mm ² conductor cross-section)
Nominal voltage	630 V (The maximum load current must not be exceeded by the total current of all connected conductors.)

Dimensions

Width	6.2 mm
-------	--------

UDK 4-MTK-P/P MIT SPERRE - Knife-disconnect terminal block



2776044

<https://www.phoenixcontact.com/us/products/2776044>

End cover width	1.5 mm
Height	63.5 mm
Depth on NS 32	52 mm
Depth on NS 35/7,5	47 mm
Depth on NS 35/15	54.5 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32

UDK 4-MTK-P/P MIT SPERRE - Knife-disconnect terminal block




2776044

<https://www.phoenixcontact.com/us/products/2776044>

Drawings

Circuit diagram



UDK 4-MTK-P/P MIT SPERRE - Knife-disconnect terminal block



2776044

<https://www.phoenixcontact.com/us/products/2776044>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2776044>



EAC

Approval ID: KZ7500651131219505

UDK 4-MTK-P/P MIT SPERRE - Knife-disconnect terminal block



2776044

<https://www.phoenixcontact.com/us/products/2776044>

Classifications

ECLASS

ECLASS-13.0	27250108
ECLASS-15.0	27250108

ETIM

ETIM 10.0	EC000902
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UDK 4-MTK-P/P MIT SPERRE - Knife-disconnect terminal block



2776044

<https://www.phoenixcontact.com/us/products/2776044>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	47aea7ec-8a7e-4436-bf6e-5f13217a54d7

EF3.1 Climate Change

CO2e kg	0.053 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com