# AXL F DI32/1 XC 1F - Digital module

2701226

https://www.phoenixcontact.com/us/products/2701226

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CRA-READY



The figure shows the standard item

Axioline F, Digital input module, Digital inputs: 32, 24 V DC, connection technology: 1-conductor, Extreme conditions version, transmission speed in the local bus: 100 Mbps, degree of protection: IP20, including bus base module and Axioline F connectors; The product is being prepared for compliance with the Cyber Resilience Act (CRA).

## Product description

The module is designed for use within an Axioline F station. It is used to acquire digital signals. You can adjust the filter times of the inputs to increase noise immunity. Filter times of 100 µs enable you to implement a counter function with a maximum input frequency of 5 kHz in the application.

## Your advantages

- 32 digital inputs in accordance with EN 61131-2 type 1 and type 3
- 24 V DC, 2.4 mA
- Connection of sensors in 1-conductor technology
- Minimum update time of < 100 µs
- Filter times can be adjusted in three increments: < 100 µs, 1000 µs or 3000 µs
- Maximum input frequency: 5 kHz
- Device rating plate stored
- Can be used under extreme ambient conditions
- Extended temperature range of -40 °C ... +70 °C (see “Tested successfully: use under extreme ambient conditions” in the data sheet)
- Partially coated PCBs


## Commercial data

| | |
|---|---|
| Item number | 2701226 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DR02 |
| Product key | DRI231 |
| GTIN | 4046356730785 |

| | |
|---|---|
| Weight per piece (including packing) | 236.9 g |
| Weight per piece (excluding packing) | 167 g |
| Customs tariff number | 85389091 |
| Country of origin | DE |

## Technical data

### Dimensions

| | |
|---|---|
| Dimensional drawing |   |
| Width | 53.6 mm |
| Height | 126.1 mm |
| Depth | 54 mm |
| Note on dimensions | The depth applies when a TH 35-7.5 DIN rail is used (in accordance with EN 60715). |

### Notes

| | |
|---|---|
| Note on application | Only for industrial use |
| Note on application | As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA. |

Utilization restriction

| | |
|---|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |

### Mounting

| | |
|---|---|
| Mounting type | DIN rail mounting |
| Mounting position | any (no temperature derating) |

### Material specifications

| | |
|---|---|
| Color (Housing) | gray (RAL 7042) |

### Interfaces

Axioline F local bus

| | |
|---|---|
| Number of interfaces | 2 |
| Connection method | Bus base module |
| Transmission speed | 100 Mbps |

### System properties

Programming data

| | |
|---|---|
| Input address area | 4 Byte |
| Output address area | 0 Byte |

Fieldbus data telegram (PROFIBUS)

| | |
|---|---|
| Required parameter data | 3 Byte |
| Required configuration data | 6 Byte |

## Input data

Digital:

| | |
|---|---|
| Input name | Digital inputs |
| Description of the input | EN 61131-2 types 1 and 3 |
| Number of inputs | 32 |
| Connection method | Push-in connection |
| Connection technology | 1-conductor |
| Input voltage range "0" signal | -3 V DC ... 5 V DC |
| Input voltage range "1" signal | 11 V DC ... 30 V DC |
| Nominal input voltage $U_{IN}$ | 24 V DC |
| Nominal input current at $U_{IN}$ | 2.4 mA |
| Current flow | linear until nominal current is reached, then constantly approx. 2. 4 mA |
| Input filter time | 3000 µs (Default) |
| | 1000 µs |
| | < 100 µs |
| Process data update | < 100 µs |
| Protective circuit | Polarity reversal protection of the inputs; parallel diode (30 V, 5 s) |

## Product properties

| | |
|---|---|
| Product type | I/O component |
| Product family | Axioline F |
| Type | block modular |
| Mounting position | any (no temperature derating) |
| Scope of supply | including bus base module and Axioline F connectors |
| Special properties | The product is being prepared for compliance with the Cyber Resilience Act (CRA) |
| | Extreme conditions version |

Insulation characteristics

| | |
|---|---|
| Overvoltage category | II (IEC 60664-1, EN 60664-1) |
| Pollution degree | 2 (IEC 60664-1, EN 60664-1) |

## Electrical properties

| | |
|---|---|
| Maximum power dissipation for nominal condition | 3.65 W |

Potentials: Axioline F local bus supply ($U_{Bus}$)

| | |
|---|---|
| Supply voltage | 5 V DC (via bus base module) |
| Current draw | max. 120 mA (HW 00) |
| | max. 60 mA (from HW 01) |

Potentials: Supply for digital input modules ($U_I$)

| | |
|---|---|
| Supply voltage | 24 V DC |
| Supply voltage range | 19.2 V DC ... 30 V DC (including all tolerances, including ripple) |
| Current draw | max. 50 mA |
| Protective circuit | Surge protection; electronic (35 V, 0.5 s) |
| | Reverse polarity protection; parallel diode; with external 5 A fuse (only for commissioning) |
| Protection | max. 8 A (polarity reversal protection up to 5 A) |

Electrical isolation/isolation of the voltage ranges

| | |
|---|---|
| Test voltage: 5 V supply of the local bus ($U_{Bus}$) / 24 V supply (I/Os) | 500 V AC, 50 Hz, 1 min |
| Test voltage: 5 V supply of the local bus ($U_{Bus}$) / functional ground | 500 V AC, 50 Hz, 1 min |
| Test voltage: 24 V supply (I/O) / functional ground | 500 V AC, 50 Hz, 1 min |

## Connection data

Connection technology

| | |
|---|---|
| Connection name | Axioline F connector |
| Note on the connection method | Please observe the information provided on conductor cross-sections in the “Axioline F: system and installation” user manual. |
| | Applications with UL approval: only use copper conductors. |

Axioline F connector

| | |
|---|---|
| Connection method | Push-in connection |
| Note on the connection method | Please observe the information provided on conductor cross-sections in the “Axioline F: system and installation” user manual. |
| | Applications with UL approval: only use copper conductors. |
| Conductor cross-section, rigid | 0.2 mm² ... 1.5 mm² |
| Conductor cross-section, flexible | 0.2 mm² ... 1.5 mm² |
| Conductor cross-section AWG | 24 ... 16 |
| Stripping length | 8 mm |

## Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -25 °C ... 60 °C (Standard applications and applications with UL approval) |
| | -40 °C ... 70 °C (Extended, see section “Tested successfully: use under extreme ambient conditions” in the data sheet.) |
| Degree of protection | IP20 |
| Air pressure (operation) | 70 kPa ... 106 kPa (up to 3000 m above sea level) |
| Air pressure (storage/transport) | 70 kPa ... 106 kPa (up to 3000 m above sea level) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |

Mechanical test

| | |
|---|---|
| Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6 | 5g |
| Shock in accordance with EN 60068-2-27/IEC 60068-2-27 | 30g |
| Continuous shock in accordance with EN 60068-2-27/IEC 60068-2-27 | 10g |

Test (noxious gas)


| | |
|---|---|
| Test standard | ISA-71.04-2013 G3 Harsh Group A |
| | IEC 60068-2-60:2015 Method 4 |
| Temperature | 25 °C ±1 K |
| Humidity (relative) | 75 % ±3 % |
| Test duration | 21 Days |
| Volume concentration $H_2S$ (Hydrogen sulfide) | 50 ppb |
| Volume concentration $NO_2$ (Nitrogen dioxide) | 1250 ppb |
| Volume concentration $Cl_2$ (Chlorine) | 10 ppb |
| Volume concentration $SO_2$ (Sulfur dioxide) | 300 ppb |

## Standards and regulations


| | |
|---|---|
| Protection class | III (IEC 61140, EN 61140, VDE 0140-1) |

## Drawings


Dimensional drawing




Connection diagram



Block diagram




Internal wiring of the terminal points

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2701226

**DNV GL**
Approval ID: TAA00000DF

**BSH**
Approval ID: 840c

**RINA**
Approval ID: ELE008423XG001

**cULus Listed**
Approval ID: E238705

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27242604 |
| ECLASS-15.0 | 27242604 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC001599 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 32151600 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| | 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1) |
| SCIP | 176effd0-e82d-4dd0-ad49-f023593c2906 |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com