

NLC-IO-03I-04QRD-05A - I/O extension module



2701328

<https://www.phoenixcontact.com/us/products/2701328>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



I/O extension module for use with Nanoline 24 V DC base unit. Equipped with 3 digital input and 4, 5 A relay output channels. A maximum of three I/O extension modules can be attached to a base unit.

Your advantages

- Automatically recognized by the firmware
- I/O modules are electrically isolated
- Up to 3 modules can be added to the right side of a base unit
- Can be powered from a secondary power supply

Commercial data

Item number	2701328
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR11
Product key	DRACAB
GTIN	4046356325493
Weight per piece (including packing)	212.4 g
Weight per piece (excluding packing)	190.5 g
Customs tariff number	85389099
Country of origin	IN

Technical data

Product properties

Product type	Extension module
Product family	Nanoline
Mounting position	Attaches to DB-9 connector on right-side of base unit

Electrical properties

Supply: Module electronics

Connection method	Screw connection
Supply voltage	24 V AC/DC
Supply current	typ. 100 mA max. 500 mA

Input data

Digital:

Input name	Digital inputs
Description of the input	PNP/NPN
Number of inputs	3
Connection method	Screw connection
Typical response time	60 μ s (on) 70 μ s (OFF)

Output data

Digital:

Output name	Relay output
Output description	Relay output
Connection method	Screw connection
Number of outputs	4
Maximum output current per channel	5 A
Maximum output current per module / terminal block	20 A
Maximum output current per module	20 A

Connection data

Connection method	Screw connection
-------------------	------------------

Dimensions

Dimensional drawing	
---------------------	--

NLC-IO-03I-04QRD-05A - I/O extension module



2701328

<https://www.phoenixcontact.com/us/products/2701328>

Width	40 mm
Height	103.5 mm
Depth	43 mm

Material specifications

Color	white
-------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	0 % ... 90 %

Mounting

Mounting type	DIN rail mounting
	DIN rail mounting
Mounting position	Attaches to DB-9 connector on right-side of base unit

NLC-IO-03I-04QRD-05A - I/O extension module


2701328

<https://www.phoenixcontact.com/us/products/2701328>



Drawings

Dimensional drawing




NLC-IO-03I-04QRD-05A - I/O extension module

2701328

<https://www.phoenixcontact.com/us/products/2701328>



Connection diagram



NLC-IO-03I-04QRD-05A - I/O extension module



2701328

<https://www.phoenixcontact.com/us/products/2701328>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2701328>



UL Listed

Approval ID: E238705



cUL Listed

Approval ID: E238705

2701328

<https://www.phoenixcontact.com/us/products/2701328>

Classifications

ECLASS

ECLASS-13.0

27242216

ETIM

ETIM 9.0

EC001417

UNSPSC

UNSPSC 21.0

39122300

2701328

<https://www.phoenixcontact.com/us/products/2701328>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	048b029c-0eea-4ecf-af3f-6477848b3849

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com