


PSM-LWL-GDM-RUGGED- 50/125 - FO cable



2799322

<https://www.phoenixcontact.com/us/products/2799322>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fiber glass cable, duplex 50 μm /125 μm , by the meter, without male connector, for installation in stationary systems and machines

The figure shows version PSM-LWL-PCF-200/230

Your advantages

- Robust installation cable for installation in stationary systems and machines
- For indoors
- Rugged polyurethane (PUR) outer sheath
- Highly tear-resistant aramid strain relief elements
- 2.9 mm individual wires made from highly flexible FRNC material
- Halogen-free, ozone, and UV resistant

Commercial data

Item number	2799322
Packing unit	1 m
Minimum order quantity	1 m
Note	Made to order (non-returnable)
Sales key	DN06
Product key	DNC233
GTIN	4017918074029
Weight per piece (including packing)	51.88 g
Weight per piece (excluding packing)	51.88 g
Customs tariff number	85447000
Country of origin	DE

PSM-LWL-GDM-RUGGED- 50/125 - FO cable



2799322

<https://www.phoenixcontact.com/us/products/2799322>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Data cable by the meter
Number of positions	2

Electrical properties

Transmission medium	Multi-mode fiberglass
---------------------	-----------------------

Interfaces

Signal	INTERBUS
	PROFIBUS
	Point-to-point
	Ethernet
	RS-485

Dimensions

External dimensions

External diameter min.	7.5 mm
External diameter max.	8.5 mm

Material specifications

Color (Outer sheath)	orange (RAL 2003)
Color (Single-core wire)	red (RAL 3001)
Outer sheath, material	PUR

Cable/line

Cable length	Free input (1.0 ... 2000 m)
Cable weight	50 kg/km
Cable abbreviation	I-V(ZN)H11Y 2G50/125 2,5B600+0,7F1200
External cable diameter	8 mm
Outer sheath, material	PUR
Single wire, material	FRNC material
Individual wire diameter	2.9 mm ±0.1 mm
Bending radius, single element	30 mm (Short-term)
	30 mm (Short-term)
Bending radius, entire cable	65 mm (Short-term)
	65 mm (Short-term)
	30 mm (Short-term)

PSM-LWL-GDM-RUGGED- 50/125 - FO cable



2799322

<https://www.phoenixcontact.com/us/products/2799322>

Bending radius	50 mm (permanent)
	65 mm (Short-term)
	65 mm (permanent)
Tensile strength short-term/long-term	1000 N / 200 N
Lateral pressure short term	400 N/cm
Lateral pressure, long-term	100 N/cm
Impact strength	2 Nm / 10 x
850 nm	2.5 dB/km
1300 nm	0.7 dB/km
Halogen-free	According to IEC 60754-2

FO cable

Fiber	Fiberglass, 50/125 µm
-------	-----------------------

Mechanical properties

Tensile strength short-term/long-term	1000 N / 200 N
---------------------------------------	----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Impact strength	2 Nm / 10 x
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Ambient temperature (installation)	-5 °C ... 50 °C
Altitude	5000 m

Mounting

cable layer type	Indoors
------------------	---------

PSM-LWL-GDM-RUGGED- 50/125 - FO cable



2799322

<https://www.phoenixcontact.com/us/products/2799322>

Classifications

ECLASS

ECLASS-13.0	27061803
ECLASS-15.0	27061803

ETIM

ETIM 10.0	EC000034
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

PSM-LWL-GDM-RUGGED- 50/125 - FO cable



2799322

<https://www.phoenixcontact.com/us/products/2799322>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.214 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com