

# PSM-SET-FSMA-LINK/2 - FO coupling

2799416

<https://www.phoenixcontact.com/us/products/2799416>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Coupling; set consisting of 2 couplings for connecting F-SMA plugs



## Your advantages

- High reliability with comprehensive quality assurance measures
- Optimized precision (stability) with the use of ceramic sleeves
- Future-proof, thanks to RoHS 2 conformity
- Tailored for compatibility with the DIN rail adapters

## Commercial data

Item number	2799416
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIDA
GTIN	4017918118396
Weight per piece (including packing)	13 g
Weight per piece (excluding packing)	10.66 g
Customs tariff number	85367000
Country of origin	DE

# PSM-SET-FSMA-LINK/2 - FO coupling



2799416

<https://www.phoenixcontact.com/us/products/2799416>

## Technical data

### Product properties

Product type	Data plug
Application	FO coupling
Type	FSMA
Sensor type	Ethernet
Number of positions	2
Connection profile	FSMA


### Electrical properties

Attenuation	< 2 dB
Transmission medium	FO

### Connection data

Connection method	Coupling
-------------------	----------

### Dimensions

Dimensional drawing	
Depth	23.5 mm
Hole diameter	6.75 mm

### Material specifications

Color	Bare metallic
Color of the housing part	silver
Material	Die-cast zinc
Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact surface material	Gold

### Cable/line

Cable type	Fiberglass
External sheath, color	silver-colored
Tensile strength short-term/long-term	40 N
Resistance to oil	yes

### FO cable

Number of fibers	2
Fiber type	GOF, PCF, POF

# PSM-SET-FSMA-LINK/2 - FO coupling



2799416

<https://www.phoenixcontact.com/us/products/2799416>

Attenuation	≤ 1.5 dB
-------------	----------

## Mechanical properties

Tensile strength short-term/long-term	40 N
---------------------------------------	------

## Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

## Characteristics

Attenuation	< 2 dB
-------------	--------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-25 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Resistance to UV radiation	yes
Resistance to oil	yes

## Standards and regulations

Resistance to oil	yes
-------------------	-----


# PSM-SET-FSMA-LINK/2 - FO coupling

2799416

<https://www.phoenixcontact.com/us/products/2799416>


## Drawings

Dimensional drawing



Dimensional drawing F-SMA coupling

Drilling plan/solder pad geometry



Drilling diagram F-SMA panel feed-through

# PSM-SET-FSMA-LINK/2 - FO coupling



2799416

<https://www.phoenixcontact.com/us/products/2799416>

## Classifications

### ECLASS

ECLASS-13.0	19170116
ECLASS-15.0	19170116

### ETIM

ETIM 10.0	EC000752
-----------	----------

### UNSPSC

UNSPSC 21.0	43223300
-------------	----------

2799416

<https://www.phoenixcontact.com/us/products/2799416>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	2.454 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)