

PSM-SET-FSMA-LINK/2 - FO coupling

2799416

<https://www.phoenixcontact.com/us/products/2799416>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Coupling; set consisting of 2 couplings for connecting F-SMA plugs



Your advantages

- High reliability with comprehensive quality assurance measures
- Optimized precision (stability) with the use of ceramic sleeves
- Future-proof, thanks to RoHS 2 conformity
- Tailored for compatibility with the DIN rail adapters

Commercial data

Item number	2799416
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIDA
GTIN	4017918118396
Weight per piece (including packing)	13 g
Weight per piece (excluding packing)	10.66 g
Customs tariff number	85367000
Country of origin	DE

PSM-SET-FSMA-LINK/2 - FO coupling

2799416

<https://www.phoenixcontact.com/us/products/2799416>

Technical data

Product properties

Product type	Data plug
Application	FO coupling
Type	FSMA
Number of positions	2
Connection profile	FSMA

Electrical properties

Attenuation	< 2 dB
Transmission medium	FO


Connection data

Connection method	Coupling
-------------------	----------

Interfaces

Signal type/category	Ethernet
----------------------	----------

Dimensions

Dimensional drawing	
Depth	23.5 mm
Hole diameter	6.75 mm

Material specifications

Color	Bare metallic
Color of the housing part	silver
Material	Die-cast zinc
Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact surface material	Gold

Cable/line

Cable type	Fiberglass
Signal type/category	Ethernet
External sheath, color	silver-colored
Tensile strength short-term/long-term	40 N
Resistance to oil	yes

PSM-SET-FSMA-LINK/2 - FO coupling



2799416

<https://www.phoenixcontact.com/us/products/2799416>

FO cable

Number of fibers	2
Fiber type	GOF, PCF, POF
Attenuation	≤ 1.5 dB

Mechanical properties

Tensile strength short-term/long-term	40 N
---------------------------------------	------

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Characteristics

Attenuation	< 2 dB
-------------	--------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-25 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Resistance to UV radiation	yes
Resistance to oil	yes

Standards and regulations

Resistance to oil	yes
-------------------	-----

PSM-SET-FSMA-LINK/2 - FO coupling




2799416

<https://www.phoenixcontact.com/us/products/2799416>


Drawings

Dimensional drawing



Dimensional drawing F-SMA coupling

Drilling plan/solder pad geometry



Drilling diagram F-SMA panel feed-through

PSM-SET-FSMA-LINK/2 - FO coupling



2799416

<https://www.phoenixcontact.com/us/products/2799416>

Classifications

ECLASS

ECLASS-13.0	19170116
ECLASS-15.0	19170116

ETIM

ETIM 10.0	EC000752
-----------	----------

UNSPSC

UNSPSC 21.0	43223300
-------------	----------

2799416

<https://www.phoenixcontact.com/us/products/2799416>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	2.454 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com