# FL VIEW 32 LITE - Network management software

2701744

https://www.phoenixcontact.com/us/products/2701744

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.




FL VIEW, SNMP-based software in English, for the detection and display of Ethernet networks. 32 nodes (network devices) can be monitored in one Class C subnetwork with this version.

## Your advantages

- Also suitable for PROFINET networks thanks to LLDP support
- Non-proprietary use also possible thanks to SNMP standard
- Special support for Phoenix Contact Factoryline devices

## Commercial data

| | |
|---|---|
| Item number | 2701744 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | DN21 |
| Product key | DNN155 |
| GTIN | 4046356807319 |
| Weight per piece (including packing) | 73.3 g |
| Weight per piece (excluding packing) | 73.3 g |
| Customs tariff number | 85234910 |
| Country of origin | DE |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Network management software |
| Scope of supply | CD-ROM with English product version and online documentation |

### System properties

| | |
|---|---|
| Intended use for the software | Network representation |
| | Diagnostics |

Functionality

| | |
|---|---|
| Basic functions | FL VIEW is a software product for detecting and monitoring industrial Ethernet TCP/IP networks with advanced features for PROFINET applications. |
| | FL VIEW automatically detects the topology and status of the networks and devices and transmits this in an animated realtime graphic. |
| Expanded functionality | 32 nodes (network devices) can be monitored in one Class C subnetwork with the FL VIEW 32 LITE version |
| Associated hardware | Ethernet infrastructure components |

System requirements

| | |
|---|---|
| Operating equipment | Keyboard, mouse recommended |
| Operating system | Windows XP SP3 (32-bit) |
| | WIndows 7 |
| | Windows® Server 2008 |
| | Windows® Server 2003 |
| Processor | > 1 GHz |
| Hard disk memory | min. 150 Mbyte (For help and video files, an additional 650 MB is needed) |
| Main memory (RAM) | 512 Mbyte |
| Interfaces | Ethernet Port |
| Languages supported | English |
| Optical drive | CD-ROM |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com