

FL RED 2003E PRP - Redundancy module



2701863

<https://www.phoenixcontact.com/us/products/2701863>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ethernet redundancy module for redundant networks with the redundancy protocol PRP and three RJ45 connections.

Product description

The compact redundancy modules (RED) enable flexible and economical design of high-availability Ethernet networks in the field of energy and automation. With robustness according to IEC 61850-3 and IEEE 1613, their wide temperature range from $-40\text{ }^{\circ}\text{C}$ to $+70\text{ }^{\circ}\text{C}$, and extensive power supply range from 18 to 58 V DC, they cover all the requirements of industrial and energy technology applications. Parallel redundancy according enables high availability networks without switch-over time to be established.

Your advantages

- Ambient temperature $-40\text{ }^{\circ}\text{C}$... $70\text{ }^{\circ}\text{C}$
- Alarm contact
- Easy startup without configuration
- Meets the requirements of IEC 61850-3 and IEEE 1613
- Low power consumption during operation
- No loss of packets in the event of a network failure
- Parallel redundancy without switch-over times for maximum availability

Commercial data

Item number	2701863
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN17
Product key	DNN143
GTIN	4046356867443
Weight per piece (including packing)	512 g
Weight per piece (excluding packing)	420 g
Customs tariff number	85176200
Country of origin	DE

FL RED 2003E PRP - Redundancy module



2701863

<https://www.phoenixcontact.com/us/products/2701863>

Technical data

Dimensions

Width	40 mm
Height	100 mm
Depth	109 mm

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Interfaces

Ethernet (RJ45)

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)
No. of channels	3 (RJ45 ports)
Data flow control/protocols	IEC 61850-3, IEEE 1613

Product properties

Product type	Switch
Product family	Redundancy module
Type	Block design

Switch functions

Basic functions	Ethernet redundancy module for the Parallel Redundancy Protocol
Redundancy	PRP (Parallel Redundancy Protocol)
Status and diagnostic indicators	LEDs: U_{S1} , U_{S2} (redundant voltage supply), link and activity per port

Security functions

Basic functions	Ethernet redundancy module for the Parallel Redundancy Protocol
-----------------	---

Electrical properties

Local diagnostics	US1, US2 Supply voltage Green LED
	LNK/ACT Link status/data transmission Green LED
Maximum power dissipation for nominal condition	6 W
Transmission medium	Copper

Supply

Supply voltage (DC)	24 V DC (redundant)
Supply voltage	48 V DC (redundant)

FL RED 2003E PRP - Redundancy module



2701863

<https://www.phoenixcontact.com/us/products/2701863>

Supply voltage range	18 V DC ... 58 V DC
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Typical current consumption	250 mA (at U _S = 24 V DC)

Supply: Module electronics

Connection method	Via COMBICON
Supply voltage	48 V DC
Supply voltage range	18 V DC ... 58 V DC

Connection data

Conductor cross-section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-45 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Air pressure (operation)	70 kPa ... 106 kPa (3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (3000 m above sea level)

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Conformance with EMC directives	IEC 61000-6-2 IEC 61000-4-2 (ESD) Criterion A
	IEC 61000-6-2 IEC 61000-4-3 (immunity to radiated interference) Criterion A
	IEC 61000-6-2 IEC 61000-4-4 (burst) Criterion A
	IEC 61000-6-2 IEC 61000-4-5 (surge) Criterion A
	IEC 61000-6-2 IEC 61000-4-6 (immunity to conducted interference) Criterion A
	IEC 61000-6-2 IEC 61000-4-8 (immunity to magnetic fields) Criterion A
Noise immunity	EN 55022 (emitted interference) Criterion B IEC 61850-3, IEEE 1613, EN 61000-6-2: 2005

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

System properties

Functionality

Basic functions	Ethernet redundancy module for the Parallel Redundancy Protocol
-----------------	---

FL RED 2003E PRP - Redundancy module



2701863

<https://www.phoenixcontact.com/us/products/2701863>

Signaling

Status display

LEDs: U_{S1} , U_{S2} (redundant voltage supply), link and activity per port

FL RED 2003E PRP - Redundancy module



2701863

<https://www.phoenixcontact.com/us/products/2701863>

Classifications

UNSPSC

UNSPSC 21.0	43201400
-------------	----------

2701863

<https://www.phoenixcontact.com/us/products/2701863>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com