

PT-IQ-1X2-TELE-P - Surge protection plug



2800782

<https://www.phoenixcontact.com/us/products/2800782>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protection plug with integrated multi-stage status indicator on the module, for protecting a double wire from analog and digital telecommunications interfaces (up to 16 Mbps).

Your advantages

- Predictive monitoring with 3-stage LED display
- Integration of the status message into the system controller via group remote signaling
- The signal is not influenced during maintenance work, thanks to the impedance-neutral insertion and removal of protective plugs
- Maximum ease of maintenance, thanks to the 2-piece design
- Maximum protection for MCR applications with high discharge capacity

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2800782 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | CL22 |
| Product key | CL2151 |
| GTIN | 4046356645270 |
| Weight per piece (including packing) | 48.6 g |
| Weight per piece (excluding packing) | 48.3 g |
| Customs tariff number | 85363010 |
| Country of origin | DE |

PT-IQ-1X2-TELE-P - Surge protection plug



2800782

<https://www.phoenixcontact.com/us/products/2800782>

Technical data

Notes

General

| | |
|------|--|
| Note | Remote signaling as well as the power supply are established by inserting the connector into the base element. |
|------|--|

Product properties

| | |
|--------------------------------|----------------------|
| Product type | Replacement plug |
| Product family | PLUGTRAB IQ |
| Type | Male |
| Surge protection fault message | Optical, multi-stage |
| Wire pairs per module | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree | 2 |


Electrical properties

| | |
|-----------------------|----------|
| Nominal voltage U_N | 180 V DC |
|-----------------------|----------|

Connection data

| | |
|-------------------|-----------|
| Connection method | pluggable |
|-------------------|-----------|

Dimensions

| | |
|------------------------|--|
| Dimensional drawing |  |
| Width | 17.7 mm |
| Height | 45 mm |
| Depth | 53.4 mm |
| Horizontal pitch | 1 Div. |
| Complete module width | 17.7 mm |
| Complete module height | 91.1 mm |
| Complete module depth | 77.5 mm |

Material specifications

| | |
|--|------------------|
| Color | black (RAL 9005) |
| | black (RAL 9005) |
| Flammability rating according to UL 94 | V-0 |
| Housing material | PA 6.6 |

Protective circuit

PT-IQ-1X2-TELE-P - Surge protection plug



2800782

<https://www.phoenixcontact.com/us/products/2800782>

| | |
|--|-------------------------------|
| Direction of action | Line-Line & Line-Earth Ground |
| Nominal voltage U_N | 180 V DC |
| Maximum continuous operating voltage U_C | 180 V DC |
| Rated current | 150 mA (25 °C) |
| Surge protection fault message | Optical, multi-stage |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Altitude | ≤ 4000 mm (amsl) |
| Permissible humidity (operation) | 5 % ... 95 % |

Standards and regulations

| | |
|--------------------------|--------------------------|
| Standards/specifications | IEC 61643-21 |
| Note | 2000 + A1:2008 + A2:2012 |
| Standards/specifications | EN 61643-21 |
| Note | 2001 + A1:2009 + A2:2013 |
| Standards/specifications | EN 61000-6-2 |
| Note | 2005 |
| Standards/specifications | EN 61000-6-3 |
| Note | 2007 + A1:2011 |

Mounting

| | |
|---------------|-----------------|
| Mounting type | on base element |
|---------------|-----------------|

PT-IQ-1X2-TELE-P - Surge protection plug

2800782

<https://www.phoenixcontact.com/us/products/2800782>



Drawings

Dimensional drawing



PT-IQ-1X2-TELE-P - Surge protection plug



2800782

<https://www.phoenixcontact.com/us/products/2800782>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27171503 |
| ECLASS-15.0 | 27171503 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001466 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

2800782

<https://www.phoenixcontact.com/us/products/2800782>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c), 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| | 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7) |
| SCIP | eada3379-72bf-4a40-af86-2e20d7852042 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 3.113 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com