

CB TM1 12A SFB P - Thermal-magnetic device circuit breaker



2800844

<https://www.phoenixcontact.com/us/products/2800844>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal-magnetic device circuit breaker, 1-pos., tripping characteristic SFB, 1 changeover contact, plug for base element.

Your advantages

- Individually adjustable with protective plugs
- Fuse protection for above-average conductor lengths with the aid of the SFB characteristic curve
- Protective plug with fixed nominal current value as protection against unintentional changes
- Increased safety with electrical isolation in the event of errors

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2800844 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | CL04 |
| Product key | CLA124 |
| GTIN | 4046356689953 |
| Weight per piece (including packing) | 43.4 g |
| Weight per piece (excluding packing) | 40.3 g |
| Customs tariff number | 85362010 |
| Country of origin | ID |

CB TM1 12A SFB P - Thermal-magnetic device circuit breaker



2800844

<https://www.phoenixcontact.com/us/products/2800844>

Technical data

Product properties

| | |
|---------------------|--|
| Product type | Thermomagnetic device circuit breakers |
| Product family | CB TM |
| Type | Male |
| Number of positions | 1 |
| No. of channels | 1 |

Insulation characteristics

| | |
|---------------------|---|
| Degree of pollution | 2 |
|---------------------|---|

Electrical properties

| | |
|-----------|------------------|
| Fuse type | Automatic device |
|-----------|------------------|

General

| | |
|---|--|
| Rated voltage | 50 V DC (IEC 60934) |
| | 50 V DC (UL 1077) |
| | 50 V DC (UL 508 - with plug-in base) |
| Rated insulation voltage U_i | 277 V AC (UL 1077) |
| | 250 V AC (IEC 60934) |
| Rated current I_N | 12 A (IEC 60934) |
| | 12 A DC (low-induction load according to UL 1077) |
| | 12 A DC (low-induction load according to UL 508 - with plug-in base) |
| Rated surge voltage | 2.5 kV (Increased insulation in actuation area) |
| Insulation resistance R_{iso} | > 100 M Ω (500 V DC) |
| Auxiliary circuit | 277 V AC / 0.5 A (Low-induction) |
| | 277 V AC / 1 A (Low-induction, maximum of 2000 cycles) |
| | 50 V DC / 1 A (Low-induction) |
| Type of actuation | S type |
| Tripping method | TM (thermal-magnetic) |
| Tripping level | Trip-free mechanism (positive) |
| Device resistance | 11 m Ω |
| Required backup fuse | 48 A ($I > I_{cn}$) |
| Rated short-circuit switching capacity I_{cn} | 600 A (50 V DC) |
| Short-circuit switching capacity | 1000 A AC (277 V AC) |
| | 1000 A DC (50 V DC) |
| Dielectric strength | 3000 V AC (Actuation area) |
| | 1500 V AC (Main to auxiliary circuit) |
| | 1500 V AC (Open main circuit) |
| | 1000 V AC (Open auxiliary circuit) |
| Switching cycles, max. | 6000 (at $1 \times I_n$) |
| Fuse | SFB |

CB TM1 12A SFB P - Thermal-magnetic device circuit breaker

2800844

<https://www.phoenixcontact.com/us/products/2800844>

| | |
|------------------------|---|
| Power dissipation | 2.88 W (in nominal operation per channel) |
| Voltage drop | 0.13 V (at $1 \times I_n$) |
| Contact switching type | 1 changeover contact |


Auxiliary contact

| | |
|---|-------|
| Minimum operating voltage U_{\min} DC | 10 V |
| Maximum operating voltage U_{\max} DC | 240 V |
| Maximum operating voltage U_{\max} AC | 240 V |
| Minimum operating current I_{\min} | 10 mA |
| Max. operating current I_{\max} | 1 A |

Connection data

| | |
|-------------------|-----------|
| Connection method | pluggable |
| Connection method | pluggable |

Dimensions

| | |
|------------------------|--|
| Dimensional drawing |  |
| Width | 12.3 mm |
| Height | 45 mm |
| Depth | 52 mm |
| Complete module width | 12.3 mm |
| Complete module height | 90 mm |
| Complete module depth | 77.3 mm |

Material specifications

| | |
|--|------------------|
| Color | gray (RAL 7042) |
| | black (RAL 9005) |
| Flammability rating according to UL 94 | V-0 |
| Insulating material group | II |

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Environmental and real-life conditions

Ambient conditions

| | |
|---|-----------------------|
| Degree of protection | IP30 (Actuation area) |
| Ambient temperature (operation) | -30 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |

CB TM1 12A SFB P - Thermal-magnetic device circuit breaker



2800844

<https://www.phoenixcontact.com/us/products/2800844>

| | |
|-----------------------|-------------------------------|
| Humidity test | 240 h, 95 % RH, 40 °C |
| Shock (operation) | 30g (IEC 60068-2-27, Test Ea) |
| Vibration (operation) | 8g (IEC 60068-2-6, Test Fc) |

Approvals

UL approval

| | |
|----------------|----------------------------|
| Identification | UL Listed UL 508 |
| | UL/C-UL Recognized UL 1077 |

CSA

| | |
|----------------|------------------------------|
| Identification | CSA CAN/CSA-C22.2 No. 235-04 |
|----------------|------------------------------|

Shipbuilding approval

| | |
|----------------|--------|
| Identification | DNV GL |
|----------------|--------|

Standards and regulations

| | |
|--------------------------|----------|
| Standards/specifications | EN 60934 |
|--------------------------|----------|

Mounting

| | |
|---------------|-----------------|
| Mounting type | on base element |
|---------------|-----------------|

CB TM1 12A SFB P - Thermal-magnetic device circuit breaker


2800844

<https://www.phoenixcontact.com/us/products/2800844>

Drawings



The figure shows the complete module consisting of a base element and connector



CB TM1 12A SFB P - Thermal-magnetic device circuit breaker

2800844

<https://www.phoenixcontact.com/us/products/2800844>

Application drawing



Diagram



Trigger characteristic in the DC range

CB TM1 12A SFB P - Thermal-magnetic device circuit breaker



2800844

<https://www.phoenixcontact.com/us/products/2800844>

Circuit diagram



CB TM1 12A SFB P - Thermal-magnetic device circuit breaker



2800844

<https://www.phoenixcontact.com/us/products/2800844>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2800844>



cUL Recognized
Approval ID: FILE E 140459



UL Recognized
Approval ID: FILE E 140459



DNV GL
Approval ID: TAE00003C7



VDE Zeichengenehmigung
Approval ID: 40034683



UL Listed
Approval ID: FILE E 172140



CCC
Approval ID: 2025010307749779



CSA
Approval ID: 2786957



cUL Listed
Approval ID: FILE E 172140



KC
Approval ID: SW05012-15002

UAE-RoHS

Approval ID: 22-09-50937

CB TM1 12A SFB P - Thermal-magnetic device circuit breaker



2800844

<https://www.phoenixcontact.com/us/products/2800844>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27140401 |
| ECLASS-15.0 | 27140401 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003538 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CB TM1 12A SFB P - Thermal-magnetic device circuit breaker



2800844

<https://www.phoenixcontact.com/us/products/2800844>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 6.14 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com