

CB TM1 1A M1 P - Thermal-magnetic device circuit breaker



2800847

<https://www.phoenixcontact.com/us/products/2800847>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal-magnetic device circuit breaker, 1-pos., tripping characteristic M1 (medium-blow), 1 changeover contact, plug for base element.

Your advantages

- Individually adjustable with protective plugs
- Switch higher starting currents with the aid of the M1 characteristic curve
- Protective plug with fixed nominal current value as protection against unintentional changes
- Increased safety with electrical isolation in the event of errors

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2800847 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | CL04 |
| Product key | CLA124 |
| GTIN | 4046356689984 |
| Weight per piece (including packing) | 44 g |
| Weight per piece (excluding packing) | 41.1 g |
| Customs tariff number | 85362010 |
| Country of origin | ID |

CB TM1 1A M1 P - Thermal-magnetic device circuit breaker



2800847

<https://www.phoenixcontact.com/us/products/2800847>

Technical data

Product properties

| | |
|---------------------|--|
| Product type | Thermomagnetic device circuit breakers |
| Product family | CB TM |
| Type | Male |
| Number of positions | 1 |
| No. of channels | 1 |

Insulation characteristics

| | |
|---------------------|---|
| Degree of pollution | 2 |
|---------------------|---|

Electrical properties

| | |
|-----------|------------------|
| Fuse type | Automatic device |
|-----------|------------------|

General

| | |
|--|---|
| Rated voltage | 50 V DC (IEC 60934) |
| | 50 V DC (UL 1077) |
| | 50 V DC (UL 508 - with plug-in base) |
| | 240 V AC (U _e according to IEC 60934) |
| | 277 V AC (UL 1077) |
| | 277 V AC (UL 508 - with plug-in base) |
| Rated insulation voltage U _i | 277 V AC (UL 1077) |
| | 250 V AC (IEC 60934) |
| Rated current I _N | 1 A (IEC 60934) |
| | 1 A (inductive load according to UL 1077) |
| | 1 A (low-induction load according to UL 1077) |
| | 1 A AC (inductive load according to UL 508 - with plug-in base) |
| | 1 A DC (low-induction load according to UL 508 - with plug-in base) |
| Rated surge voltage | 2.5 kV (Increased insulation in actuation area) |
| Insulation resistance R _{iso} | > 100 MΩ (500 V DC) |
| Auxiliary circuit | 277 V AC / 0.5 A (Low-induction) |
| | 277 V AC / 1 A (Low-induction, maximum of 2000 cycles) |
| | 50 V DC / 1 A (Low-induction) |
| Type of actuation | S type |
| Tripping method | TM (thermal-magnetic) |
| Tripping level | Trip-free mechanism (positive) |
| Device resistance | 1100 mΩ |
| Required backup fuse | 15 A (I > I _{cn}) |
| Rated short-circuit switching capacity I _{cn} | 300 A (240 V AC) |
| | 600 A (50 V DC) |
| Short-circuit switching capacity | 1000 A AC (277 V AC) |
| | 1000 A DC (50 V DC) |

CB TM1 1A M1 P - Thermal-magnetic device circuit breaker

2800847

<https://www.phoenixcontact.com/us/products/2800847>

| | |
|------------------------|--|
| Dielectric strength | 3000 V AC (Actuation area) |
| | 1500 V AC (Main to auxiliary circuit) |
| | 1500 V AC (Open main circuit) |
| | 1000 V AC (Open auxiliary circuit) |
| Switching cycles, max. | 6000 (at 1 x I _n) |
| | 50 (at 1.5 x I _n) |
| | 40 (at 6 x I _n) |
| Fuse | M1 (normal blow) |
| Power dissipation | 1.1 W (in nominal operation per channel) |
| Voltage drop | 1.1 V (at 1 x I _n) |
| Contact switching type | 1 changeover contact |


Auxiliary contact

| | |
|---|-------|
| Minimum operating voltage U _{min} DC | 10 V |
| Maximum operating voltage U _{max} DC | 240 V |
| Maximum operating voltage U _{max} AC | 240 V |
| Minimum operating current I _{min} | 10 mA |
| Max. operating current I _{max} | 1 A |

Connection data

| | |
|-------------------|-----------|
| Connection method | pluggable |
| Connection method | pluggable |

Dimensions

| | |
|------------------------|--|
| Dimensional drawing |  |
| Width | 12.3 mm |
| Height | 45 mm |
| Depth | 52 mm |
| Complete module width | 12.3 mm |
| Complete module height | 90 mm |
| Complete module depth | 77.3 mm |

Material specifications

| | |
|--|------------------|
| Color | gray (RAL 7042) |
| | black (RAL 9005) |
| Flammability rating according to UL 94 | V-0 |
| Insulating material group | II |

Mechanical properties

CB TM1 1A M1 P - Thermal-magnetic device circuit breaker



2800847

<https://www.phoenixcontact.com/us/products/2800847>

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Degree of protection | IP30 (Actuation area) |
| Ambient temperature (operation) | -30 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Humidity test | 240 h, 95 % RH, 40 °C |
| Shock (operation) | 30g (According to IEC 60068-2-27, Test Ea) |
| Vibration (operation) | 8g (in accordance with IEC 60068-2-6, Test Fc) |

Approvals

UL approval

| | |
|----------------|----------------------------|
| Identification | UL Listed UL 508 |
| | UL/C-UL Recognized UL 1077 |

CSA

| | |
|----------------|------------------------------|
| Identification | CSA CAN/CSA-C22.2 No. 235-04 |
|----------------|------------------------------|

Shipbuilding approval

| | |
|----------------|--------|
| Identification | DNV GL |
|----------------|--------|

Standards and regulations

| | |
|--------------------------|----------|
| Standards/specifications | EN 60934 |
|--------------------------|----------|

Mounting

| | |
|---------------|-----------------|
| Mounting type | on base element |
|---------------|-----------------|

CB TM1 1A M1 P - Thermal-magnetic device circuit breaker

2800847

<https://www.phoenixcontact.com/us/products/2800847>

Drawings



The figure shows the complete module consisting of a base element and connector



CB TM1 1A M1 P - Thermal-magnetic device circuit breaker



2800847

<https://www.phoenixcontact.com/us/products/2800847>

Application drawing



Diagram



Trigger characteristic
 Gray: DC range, blue: AC range

CB TM1 1A M1 P - Thermal-magnetic device circuit breaker



2800847

<https://www.phoenixcontact.com/us/products/2800847>

Circuit diagram



CB TM1 1A M1 P - Thermal-magnetic device circuit breaker



2800847

<https://www.phoenixcontact.com/us/products/2800847>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2800847>



cUL Recognized
Approval ID: FILE E 140459



UL Recognized
Approval ID: FILE E 140459



DNV GL
Approval ID: TAE00003C7



VDE Zeichengenehmigung
Approval ID: 40034683



UL Listed
Approval ID: FILE E 172140



CCC
Approval ID: 2025010307749779



CSA
Approval ID: 2786957



cUL Listed
Approval ID: FILE E 172140



KC
Approval ID: SW05012-15001A

UAE-RoHS

Approval ID: 22-09-50937

CB TM1 1A M1 P - Thermal-magnetic device circuit breaker



2800847

<https://www.phoenixcontact.com/us/products/2800847>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27140401 |
| ECLASS-15.0 | 27140401 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003538 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CB TM1 1A M1 P - Thermal-magnetic device circuit breaker



2800847

<https://www.phoenixcontact.com/us/products/2800847>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 6.107 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com