

# IB STME 24 BAI 8/EF - Replacement electronics module

2701956

<https://www.phoenixcontact.com/us/products/2701956>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



INTERBUS-ST analog input module, 8 inputs, 0 - 5 V, 0 - 10 V, 0 - 25 V, 0 - 50 V, 0 - 20 mA, 4 - 20 mA, 0 - 40 mA, 0 - 60 mA, degree of protection IP20, comprising: Module electronics only

## Your advantages

- 8 analog inputs for the connection of either voltage or current signals
- Connection of sensors in 2-conductor technology

## Commercial data

Item number	2701956
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRI341
GTIN	4046356895750
Weight per piece (including packing)	249.7 g
Weight per piece (excluding packing)	249.7 g
Country of origin	DE

# IB STME 24 BAI 8/EF - Replacement electronics module



2701956

<https://www.phoenixcontact.com/us/products/2701956>

## Technical data

### Interfaces

#### ST local bus

No. of channels	2
Connection method	ST local bus connector
Transmission speed	500 kbps
Transmission physics	Copper

### System properties

#### Module

ID code (dec.)	127
ID code (hex)	7F
Length code (hex)	4
Length code (dec)	4
Input address area	8 Byte
Output address area	0 Byte
Register length	8 Byte

### Input data

#### Analog:

Input name	Analog inputs
Number of inputs	max. 8 (Voltage or current)
A/D conversion time	max. 10 $\mu$ s (per channel)
Connection technology	2, 3-conductor
Measuring principle	Successive approximation
Measured value representation	8 bit straight binary (default) or 12 bit two's complement (can be parameterized)

#### Analog:

Number of inputs	8 (Voltage inputs)
Voltage input signal	0 V ... 10 V
	0 V ... 5 V
	0 V ... 25 V
	0 V ... 50 V
Input resistance of voltage input	150 k $\Omega$
A/D converter resolution	12 bit (4096 steps; 2.44 mV/quantization steps)
	8 bit (256 steps; 39 mV/quantization steps)

#### Analog:

Number of inputs	8 (Current inputs)
A/D conversion time	max. 10 $\mu$ s
	4 mA ... 20 mA

# IB STME 24 BAI 8/EF - Replacement electronics module



2701956

<https://www.phoenixcontact.com/us/products/2701956>

Current input signal	0 mA ... 20 mA
	0 mA ... 40 mA
	0 mA ... 60 mA (rms)
	0 mA ... 100 mA (peak)
Input resistance current input	77 $\Omega$
A/D converter resolution	12 bit (4096 steps; 3.91 $\mu$ A/quantization steps)
	8 bit (256 steps; 62.7 $\mu$ A/quantization steps)

## Product properties

Product type	I/O component
Type	modular
	INTERBUS Smart Terminal
Operating mode	Process data mode with 4 words
Diagnostics messages	Failure of the internal I/O supply I/O error message sent to the bus coupler
	F1 fuse failure I/O error message sent to the bus coupler
	I/O supply failure I/O error message sent to the bus coupler

## Electrical properties

### Supply: Module electronics

Connection method	ST local bus connector
Designation	Communications power
Supply voltage	9 V DC (from the ST local bus)
Current consumption	typ. 54 mA
	max. 80 mA
Power consumption	typ. 0.5 W

### Supply:

Designation	$U_S$
Supply voltage	24 V DC
Supply voltage range	19.5 V DC ... 30.2 V DC (including all tolerances, including ripple)
Current consumption	typ. 45 mA ( $I_b = 0$ mA ( $I_b =$ total current for supplying passive sensors for all channels))
	typ. 120 mA ( $I_b = 100$ mA ( $I_b =$ total current for supplying passive sensors for all channels))

### Supply: Passive sensor supply

Designation	$U_B$ (generated internally)
Supply voltage	15 V $\pm$ 6 %
Current consumption	max. 100 mA (Total for all channels)

### Electrical isolation/isolation of the voltage ranges

Test voltage: Bus/Inputs	500 V AC, 50 Hz, 1 min
Test voltage: Supply voltage/inputs	500 V AC, 50 Hz, 1 min
Test voltage: Supply voltage/Ground conductor	500 V AC, 50 Hz, 1 min
Test voltage: I/O voltage/Ground conductor	500 V AC, 50 Hz, 1 min

# IB STME 24 BAI 8/EF - Replacement electronics module



2701956

<https://www.phoenixcontact.com/us/products/2701956>

## Connection data

Connection method	Snap on
-------------------	---------

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	80 kPa ... 106 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	80 kPa ... 106 kPa (up to 2000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IB STME 24 BAI 8/EF - Replacement electronics module



2701956

<https://www.phoenixcontact.com/us/products/2701956>

## Classifications

### ECLASS

ECLASS-13.0	27242601
ECLASS-15.0	27242601

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

# IB STME 24 BAI 8/EF - Replacement electronics module



2701956

<https://www.phoenixcontact.com/us/products/2701956>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

### EF3.1 Climate Change

CO2e kg	0.563 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)