

CN-UB-280DC-3-SB - Surge protection device



2801051

<https://www.phoenixcontact.com/us/products/2801051>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Attachment plug with replaceable surge protection for coaxial signal interfaces. Connection: N connector plug/socket

Your advantages

- For outdoor installations
- Mounting plate enables mounting, e.g., in a control cabinet
- Replaceable, gas-filled arrester
- Installed as surge protection between antenna and wireless module

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2801051 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | CL25 |
| Product key | CL3311 |
| GTIN | 4046356675734 |
| Weight per piece (including packing) | 163.7 g |
| Weight per piece (excluding packing) | 145 g |
| Customs tariff number | 85363010 |
| Country of origin | CN |

CN-UB-280DC-3-SB - Surge protection device

2801051

<https://www.phoenixcontact.com/us/products/2801051>

Technical data

Product properties

| | |
|--------------------------------|--|
| Product type | Surge protection for transceiver systems |
| IEC test classification | C2 |
| | C3 |
| | D1 |
| Type | Intermediate plug |
| Number of positions | 1 |
| Surge protection fault message | none |


Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree | 2 |

Connection data

| | |
|-------------------|------------------|
| Connection method | N connector 50 Ω |
|-------------------|------------------|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 31 mm |
| Height | 33.5 mm |
| Length | 56.8 mm |

Material specifications

| | |
|----------------------------------|------------------|
| Color | nickel color |
| | black (RAL 9005) |
| Housing material | HPb59-1 |
| Housing surface material | Cu-Sn-Zn |
| Contact surface material | Au |
| Inner conductor material | QSn6.5-0.1 |
| Inner conductor surface material | Gold |
| Insulation body material | PTFE |
| Spring contact material | QSn6.5-0.1 |

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Protective circuit

| | |
|---------------------|--------------------------|
| Direction of action | Line-Shield/Earth Ground |
|---------------------|--------------------------|

CN-UB-280DC-3-SB - Surge protection device



2801051

<https://www.phoenixcontact.com/us/products/2801051>

| | |
|--|---|
| Maximum continuous operating voltage U_C | 280 V DC |
| Maximum continuous voltage U_C (line-earth) | 280 V DC |
| Rated current | 5 A (25 °C) |
| Operating effective current I_C at U_C | $\leq 1 \mu\text{A}$ |
| Nominal discharge current I_n (8/20) μs (line-ground) | 20 kA |
| Nominal discharge current I_n (8/20) μs (line-shield) | 20 kA |
| Pulse discharge current I_{imp} (10/350) μs | 2.5 kA |
| Total surge current (10/350) μs | 2.5 kA |
| Total discharge current I_{Total} (8/20) μs | 20 kA |
| Max. discharge current I_{max} (8/20) μs maximum (line-earth) | 20 kA |
| Max. discharge current I_{max} (8/20) μs maximum (line-shield) | 20 kA |
| Nominal pulse current I_{an} (10/1000) μs (line-shield) | 100 A |
| Output voltage limitation at 1 kV/ μs (line-earth) spike | $\leq 900 \text{ V}$ |
| Output voltage limitation at 1 kV/ μs (line-shield) spike | $\leq 900 \text{ V}$ |
| Voltage protection level U_p (line-earth) | $\leq 900 \text{ V}$ (C1 - 1 kV / 500 A) |
| | $\leq 1.1 \text{ kV}$ (C2 - 10 kV / 5 kA) |
| Voltage protection level U_p (line-shield) | $\leq 900 \text{ V}$ (C1 - 1 kV / 500 A) |
| | $\leq 1.1 \text{ kV}$ (C2 - 10 kV / 5 kA) |
| Response time t_A (line-earth) | $\leq 100 \text{ ns}$ |
| Response time t_A (line-shield) | $\leq 100 \text{ ns}$ |
| Input attenuation aE, asym. | typ. 0.1 dB ($\leq 3 \text{ GHz}$) |
| Cut-off frequency f_g (3 dB), asym. (shield) in 50 Ω system | $> 3 \text{ GHz}$ |
| Frequency range | 0 Hz ... 3 GHz |
| Voltage standing wave ratio VSWR in a 50 Ω system | typ. 1.15 ($\leq 3 \text{ GHz}$) |
| | max. 1.20 |
| Permissible HF power P_{max} at VSWR = xx (50 ohm system) | 700 W (VSWR = 1.1) |
| | 200 W (VSWR = ∞) |
| Capacity (Core-Earth) | typ. 1.5 pF |
| Capacity asymmetrical (shield) | typ. 1.5 pF |
| Surge protection fault message | none |
| Impulse durability (line-earth) | C2 - 10 kV / 5 kA |
| | C3 - 100 A |
| | D1 - 2.5 kA |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Degree of protection | IP55 |
| Ambient temperature (operation) | -40 °C ... 80 °C |
| Altitude | 2000 m |

Standards and regulations

Air clearances and creepage distances

| | |
|-----------------------|-------------|
| Standards/regulations | IEC 60664-1 |
|-----------------------|-------------|

CN-UB-280DC-3-SB - Surge protection device



2801051

<https://www.phoenixcontact.com/us/products/2801051>


| | |
|--------------------------|-----------------|
| Standards/specifications | IEC 61643-21/A1 |
| Note | 2008 |
| Standards/specifications | EN 61643-21/A1 |
| Note | 2009 |

Mounting

| | |
|---------------|---|
| Mounting type | Connection-specific intermediate plugging |
|---------------|---|


Drawings

Dimensional drawing




Dimensional drawing
CN-UB-280DC-3-SB

Diagram



Diagram




CN-UB-280DC-3-SB - Surge protection device



2801051

<https://www.phoenixcontact.com/us/products/2801051>

Circuit diagram



Circuit diagram

CN-UB-280DC-3-SB - Surge protection device



2801051

<https://www.phoenixcontact.com/us/products/2801051>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27171504 |
| ECLASS-15.0 | 27171504 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001466 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

CN-UB-280DC-3-SB - Surge protection device



2801051

<https://www.phoenixcontact.com/us/products/2801051>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | b6cd5d6a-c359-418b-b9f9-8cccb5b23e76 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 4.809 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com