

PT-IQ-1X2-TELE-PT - Surge protection device



2801290

<https://www.phoenixcontact.com/us/products/2801290>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protective device, consisting of plug and base element, with integrated multi-stage status indicator on the module, for protecting a double wire for analog and digital telecommunications interfaces (VDSL up to 50 Mbps, on short paths (<300 m) up to 100 Mbps). Can be used in safety-related circuits up to SIL 3.

Your advantages

- Predictive monitoring with 3-stage LED display
- Integration of the status message into the system controller via group remote signaling
- Install quickly and error-free with DIN rail connectors
- Maximum ease of maintenance, thanks to the 2-piece design
- Maximum protection for MCR applications with high discharge capacity

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2801290 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | CL22 |
| Product key | CL2153 |
| GTIN | 4046356766715 |
| Weight per piece (including packing) | 113.2 g |
| Weight per piece (excluding packing) | 108.9 g |
| Customs tariff number | 85363010 |
| Country of origin | DE |

PT-IQ-1X2-TELE-PT - Surge protection device



2801290

<https://www.phoenixcontact.com/us/products/2801290>

Technical data

Notes

General

| | |
|------|---|
| Note | Remote signaling as well as the power supply of the DIN rail connector are established by snapping the module into place on the DIN rail connector. |
|------|---|

Product properties

| | |
|--------------------------------|---|
| Product type | Surge protection for information technology |
| Product family | PLUGTRAB IQ |
| IEC test classification | B2 C1 C2 C3 D1 |
| VDE requirement class | B2 C1 C2 C3 D1 |
| Type | DIN rail module, two-section, divisible |
| Surge protection fault message | Optical, multi-stage |
| Wire pairs per module | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree | 2 |

Electrical properties

| | |
|-----------------------|----------|
| Nominal voltage U_N | 180 V DC |
|-----------------------|----------|

Connection data

| | |
|----------------------------------|---|
| Connection method | Push-in connection |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Dimensions

PT-IQ-1X2-TELE-PT - Surge protection device



2801290

<https://www.phoenixcontact.com/us/products/2801290>

| | |
|---------------------|---------------------------------|
| Dimensional drawing | |
| Width | 17.7 mm |
| Height | 109.3 mm |
| Depth | 77.5 mm (incl. DIN rail 7.5 mm) |
| Horizontal pitch | 1 Div. |

Material specifications

| | |
|--|------------------|
| Color | black (RAL 9005) |
| | black (RAL 9005) |
| Flammability rating according to UL 94 | V-0 |
| Housing material | PA 6.6 |

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Protective circuit

| | |
|---|-------------------------------|
| Direction of action | Line-Line & Line-Earth Ground |
| Nominal voltage U_N | 180 V DC |
| Maximum continuous operating voltage U_C | 180 V DC |
| Rated current | 150 mA (25 °C) |
| Operating effective current I_C at U_C | $\leq 1 \mu A$ |
| Protective conductor current I_{PE} | $\leq 1 \mu A$ |
| Nominal discharge current I_n (8/20) μs (line-line) | 10 kA |
| Nominal discharge current I_n (8/20) μs (line-ground) | 10 kA |
| Pulse discharge current I_{imp} (10/350) μs (line-earth) | 2.5 kA |
| Total discharge current I_{Total} (8/20) μs | 20 kA |
| Voltage protection level U_p (line-line) | ≤ 290 V (B2 - 100 A) |
| | ≤ 290 V (C1 - 1 kV) |
| | ≤ 290 V (C2 - 10 kV) |
| | ≤ 300 V (C2 - 10 kA) |
| | ≤ 290 V (C3 - 50 A) |
| Voltage protection level U_p (line-earth) | ≤ 500 V (B2 - 100 A) |
| | ≤ 600 V (C1 - 1 kV) |
| | ≤ 600 V (C2 - 10 kV) |
| | ≤ 650 V (C2 - 10 kA) |
| | ≤ 700 V (C3 - 50 A) |
| Response time t_A (line-line) | ≤ 1 ns |
| Response time t_A (line-earth) | ≤ 100 ns |

PT-IQ-1X2-TELE-PT - Surge protection device



2801290

<https://www.phoenixcontact.com/us/products/2801290>

| | |
|--|---|
| Input attenuation aE, sym. | typ. 0.3 dB (≤ 5 MHz / 150 Ω) |
| Cut-off frequency f _g (3 dB), sym. in 150 Ω system | typ. 25 MHz |
| Capacity (Core-Core) | typ. 60 pF |
| Resistance per path | 1.2 $\Omega \pm 5$ % |
| Surge protection fault message | Optical, multi-stage |
| Max. required back-up fuse | 150 mA (slow-blow) |
| Impulse durability (line-line) | C1 - 500 A |
| | C2 - 10 kA |
| | C3 - 50 A |
| | B2 - 100 A |
| Impulse durability (line-earth) | C1 - 500 A |
| | C2 - 10 kA |
| | C3 - 50 A |
| | B2 - 100 A |
| | D1 - 2.5 kA |
| Pulse reset time (line-line) | ≤ 30 ms |

Environmental and real-life conditions

Ambient conditions

| | |
|---|----------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Altitude | ≤ 4000 m (amsl) |

Standards and regulations

| | |
|--------------------------|--------------------------|
| VDE requirement class | B2 |
| | C1 |
| | C2 |
| | C3 |
| | D1 |
| Standards/specifications | IEC 61643-21 |
| Note | 2000 + A1:2008 + A2:2012 |
| Standards/specifications | EN 61643-21 |
| Note | 2001 + A1:2009 + A2:2013 |
| Standards/specifications | EN 61000-6-2 |
| Note | 2005 |
| Standards/specifications | EN 61000-6-3 |
| Note | 2007 + A1:2011 |

Mounting

| | |
|---------------|-----------------|
| Mounting type | DIN rail: 35 mm |
|---------------|-----------------|

PT-IQ-1X2-TELE-PT - Surge protection device




2801290

<https://www.phoenixcontact.com/us/products/2801290>

Drawings

Dimensional drawing




Schematic diagram

| Category | PT-IQ-2X2+F-...DC-UT(PT) | | | | | | | | |
|--|--------------------------|---------------------------|--------------------------|-------|--------------------------|----------------------------|------|--------------------------|-------|
| | 1oo1 architecture, HFT=0 | | | | 1oo2 architecture, HFT=1 | | | | |
| | PFD _{AVG} | PFH | Used budget of SIL 2 SIF | | PFD _{AVG} | PFH | CCF | Used budget of SIL 3 SIF | |
| | 1.07·10 ⁻⁵ | 1.90·10 ⁻⁹ 1/h | PFD _{AVG} | PFH | 5.34·10 ⁻⁷ | 9.50·10 ⁻¹¹ 1/h | 5 % | PFD _{AVG} | PFH |
| | | | 0.1 % | 0.2 % | 1.07·10 ⁻⁶ | 1.90·10 ⁻¹⁰ 1/h | 10 % | 0.1 % | 0.1 % |
| Calculation based on exida report, Phoenix Contact 13/04-032 R017 V4R0 exida Profile 1, FMEDA Analysis 2, T _{proof} : 1 year, MT: 10 years, MTTR: 24 hours, PTC: 99% Used standards IEC/EN 61508, edition 2010 (device specific) IEC/EN 61511, edition 2016 + COR1:2016 + A1:2017 (system specific) | | | | | | | | | |

Functional safety scenarios

Table also applies to the PT-IQ-1X2-TELE-UT(PT) item group

Diagram




PT-IQ-1X2-TELE-PT - Surge protection device



2801290

<https://www.phoenixcontact.com/us/products/2801290>

Circuit diagram



PT-IQ-1X2-TELE-PT - Surge protection device



2801290

<https://www.phoenixcontact.com/us/products/2801290>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2801290>



UL Listed

Approval ID: FILE E 477688



cUL Listed

Approval ID: FILE E 477688

Functional Safety

Approval ID: 13-04-032 R017 V4R0

PT-IQ-1X2-TELE-PT - Surge protection device



2801290

<https://www.phoenixcontact.com/us/products/2801290>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27171503 |
| ECLASS-15.0 | 27171503 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001466 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

2801290

<https://www.phoenixcontact.com/us/products/2801290>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c), 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| | 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7) |
| SCIP | 5ff2fe38-430e-4dc0-9cde-626613d6ed2a |

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com