

IB STME 24 TEMP 4 RTD - Replacement electronics module



2701958

<https://www.phoenixcontact.com/us/products/2701958>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



INTERBUS-ST analog input module, 4 inputs, RTD, 2-, 3-, and 4-conductor connection, IP20 degree of protection, consisting of: module electronics only

Product description

The module is designed for use within an ST station.
It is used to acquire signals from resistive temperature sensors.

Your advantages

- 4 analog input channels for connecting resistance temperature detectors (RTDs)

Commercial data

Item number	2701958
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRI343
GTIN	4046356895873
Weight per piece (including packing)	241.7 g
Weight per piece (excluding packing)	241.7 g
Country of origin	DE

IB STME 24 TEMP 4 RTD - Replacement electronics module



2701958

<https://www.phoenixcontact.com/us/products/2701958>

Technical data

Interfaces

ST local bus

No. of channels	2
Connection method	ST local bus connector
Transmission speed	500 kbps
Transmission physics	Copper

Input data

Analog:

Input name	Analog RTD inputs
Description of the input	Inputs for resistive temperature sensors
Number of inputs	4 (for resistance temperature detectors)
Connection technology	2-, 3-, 4-conductor (shielded)
A/D converter resolution	24 bit
Sensor types (RTD) that can be used	Pt 100, Pt 1000, Ni 100, Ni 1000
Measuring principle	Sigma/Delta process
Measured value representation	16 bit two's complement

Product properties

Product type	I/O component
Type	modular INTERBUS Smart Terminal
Operating mode	Process data mode with 4 words
Diagnostics messages	Failure of the internal I/O supply I/O error message sent to the bus coupler F1 fuse failure I/O error message sent to the bus coupler I/O supply failure I/O error message sent to the bus coupler

Electrical properties

Supply: Module electronics

Connection method	ST local bus connector
Designation	Communications power
Supply voltage	9 V DC (from the ST local bus)
Current consumption	typ. 54 mA max. 80 mA
Power consumption	typ. 0.5 W

Supply:

Designation	U_S
Supply voltage	24 V DC
Supply voltage range	19.5 V DC ... 30.2 V DC (including all tolerances, including ripple)

IB STME 24 TEMP 4 RTD - Replacement electronics module



2701958

<https://www.phoenixcontact.com/us/products/2701958>

Current consumption	typ. 15 mA
---------------------	------------

Electrical isolation/isolation of the voltage ranges

Test voltage: Bus/Inputs	500 V AC, 50 Hz, 1 min
Test voltage: Supply voltage/inputs	500 V AC, 50 Hz, 1 min
Test voltage: Supply voltage/Ground conductor	500 V AC, 50 Hz, 1 min
Test voltage: I/O voltage/Ground conductor	500 V AC, 50 Hz, 1 min

Connection data

Connection method	Snap on
-------------------	---------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	80 kPa ... 106 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	80 kPa ... 106 kPa (up to 2000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB STME 24 TEMP 4 RTD - Replacement electronics module



2701958

<https://www.phoenixcontact.com/us/products/2701958>

Classifications

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

IB STME 24 TEMP 4 RTD - Replacement electronics module



2701958

<https://www.phoenixcontact.com/us/products/2701958>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com