

NLC-IO-03I-04QRA-05A - I/O extension module



2701960

<https://www.phoenixcontact.com/us/products/2701960>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



I/O extension module for use with Nanoline 100...240 V AC base unit. Equipped with three digital inputs and four 5 A relay output channels. A maximum of three I/O extension modules can be attached to a base unit.

Your advantages

- Automatically recognized by the firmware
- I/O modules are electrically isolated
- Up to 3 modules can be added to the right side of a base unit
- Can be powered from a secondary power supply

Commercial data

Item number	2701960
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR11
Product key	DRACAB
GTIN	4055626002620
Weight per piece (including packing)	201.5 g
Weight per piece (excluding packing)	201.5 g
Customs tariff number	85371098
Country of origin	IN

2701960

<https://www.phoenixcontact.com/us/products/2701960>

Technical data

Product properties

Product type	Extension module
Product family	Nanoline

Electrical properties

Supply: Module electronics

Connection method	Screw connection
Supply voltage	120 V AC/DC
Supply current	typ. 16 mA

Input data

Digital:

Input name	Digital inputs
Description of the input	AC
Number of inputs	3
Connection method	Screw connection
Typical response time	850 μ s (on)
	960 μ s (OFF)

Output data

Digital:

Output name	Relay output
Output description	Relay output
Connection method	Screw connection
Number of outputs	4
Maximum output current per channel	5 A
Maximum output current per module / terminal block	20 A
Maximum output current per module	20 A

Dimensions

Dimensional drawing	
Width	40 mm
Height	103.5 mm
Depth	43 mm

Environmental and real-life conditions

NLC-IO-03I-04QRA-05A - I/O extension module



2701960

<https://www.phoenixcontact.com/us/products/2701960>

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Ambient temperature (storage/transport)	-25 °C ... 85 °C

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

NLC-IO-03I-04QRA-05A - I/O extension module




2701960

<https://www.phoenixcontact.com/us/products/2701960>

Drawings

Dimensional drawing




NLC-IO-03I-04QRA-05A - I/O extension module



2701960

<https://www.phoenixcontact.com/us/products/2701960>

Connection diagram



NLC-IO-03I-04QRA-05A - I/O extension module



2701960

<https://www.phoenixcontact.com/us/products/2701960>

Classifications

ECLASS

ECLASS-13.0

27242216

ETIM

ETIM 9.0

EC001417

UNSPSC

UNSPSC 21.0

39122300

2701960

<https://www.phoenixcontact.com/us/products/2701960>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	8(b)

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Cadmium oxide(CAS: n/a)
SCIP	58414187-c803-423a-9303-c5df7cb7d6e0

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com