

PLD T 358 W-43K-WQ/P - LED light



2702040

<https://www.phoenixcontact.com/us/products/2702040>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

LED light for use in wind turbine generators.



Product description

The LED light is designed to illuminate the interior of wind turbine generator towers.

Your advantages

- Degree of protection IP65
- Two-level operation
- Color temperature 4300 K

Commercial data

Item number	2702040
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN16
Product key	DRL241
GTIN	4046356909006
Weight per piece (including packing)	980 g
Weight per piece (excluding packing)	980 g
Customs tariff number	94054039
Country of origin	DE

PLD T 358 W-43K-WQ/P - LED light

2702040

<https://www.phoenixcontact.com/us/products/2702040>

Technical data

Product properties

Product type	Light
Application	Wind turbine generators

Electrical properties

Supply: Module electronics


Supply voltage range	220 V AC ... 240 V AC
Power consumption	15 W

Signaling

Light properties

Source of light type	LED
Number of LEDs	8
Color temperature	4300 K
Luminous flux	1250 lm

Dimensions

Dimensional drawing	
Width	85 mm
Height	100 mm
Length	460 mm

Material specifications

Color	black/white
Material	Plastic

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 55 °C
Degree of protection	IP65

PLD T 358 W-43K-WQ/P - LED light




2702040

<https://www.phoenixcontact.com/us/products/2702040>

Drawings

Dimensional drawing



Mounting information for the retaining bracket

PLD T 358 W-43K-WQ/P - LED light



2702040

<https://www.phoenixcontact.com/us/products/2702040>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com