

FL MGUARD RS2000 TX/TX-B - Router



2702139

<https://www.phoenixcontact.com/us/products/2702139>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Router, 10/100 Mbps, NAT



The figure shows the standard item

Your advantages

- Central management tool
- Maximum performance
- Maximum security

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2702139 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN28 |
| Product key | DNN321 |
| GTIN | 4046356983242 |
| Weight per piece (including packing) | 880 g |
| Weight per piece (excluding packing) | 725 g |
| Customs tariff number | 85176200 |
| Country of origin | DE |

Technical data

Dimensions

| | |
|--------|----------|
| Width | 45 mm |
| Height | 130 mm |
| Depth | 120.6 mm |

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Material specifications

| | |
|------------------|----------------------------|
| Color (Housing) | white aluminium (RAL 9006) |
| Housing material | Metal |

Interfaces

Ethernet

| | |
|----------------------|--|
| Connection method | RJ45 |
| Transmission speed | 10/100 Mbps |
| Transmission physics | Ethernet in RJ45 twisted pair |
| Transmission length | 100 m (per segment) |
| Signal LEDs | Supply voltage, data transmission, error, link, activity |
| No. of channels | 2 (RJ45 ports) |

Signal contact

| | |
|-------------------|---------------------------------------|
| Connection method | Plug-in/screw connection via COMBICON |
| Additional text | not electrically isolated |

System properties

Functionality

| | |
|-----------------|---|
| Basic functions | Router for standard routing, NAT, 1:1-NAT and port forwarding |
|-----------------|---|

Product properties

| | |
|--------------|----------------------------------|
| Product type | Security router for the DIN rail |
| Type | Stand-alone |

Security functions

| | |
|--|---|
| Data integrity | MD5, SHA-1, SHA 256, SHA-512 |
| Dynamic Host Configuration Protocol (DHCP) support | Server or Relay Agent |
| Basic functions | Router for standard routing, NAT, 1:1-NAT and port forwarding |
| Link Layer Discovery Protocol (LLDP) | As per protocol 802.2 |
| Network Time Protocol (NTP) client | Client |
| Remote Syslog Logging | on external server |

| | |
|--------------------|---|
| Routing | Standard routing, NAT, 1:1-NAT, port forwarding |
| Protection against | IP spoofing |

Electrical properties

| | |
|---|-------|
| Maximum power dissipation for nominal condition | 2.4 W |
|---|-------|

Supply

| | |
|-----------------------------|--|
| Supply voltage (DC) | 24 V DC |
| Supply voltage range | 11 V DC ... 36 V DC |
| Power supply connection | Via COMBICON, max. conductor cross-section 2.5 mm ² |
| Residual ripple | 3.6 V _{PP} (within the permitted voltage range) |
| Max. current consumption | 0.24 A |
| Typical current consumption | 100 mA (at U _S = 24 V DC) |

Function

| | |
|--------------------------------|------------------------------|
| Signal contact control voltage | 24 V DC (typical) |
| Signal contact control current | 250 mA (short-circuit-proof) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -20 °C ... 60 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

EMC data

| | |
|---------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC Directive 2014/30/EU |
| Conformance with EMC directives | IEC 61000-6-2 IEC 61000-4-2 (ESD) 6 kV contact discharge, 8 kV air discharge |
| | IEC 61000-6-2 IEC 61000-4-3 (immunity to radiated interference) 10 V/m (80 MHz ... 2000 MHz) |
| | IEC 61000-6-2 IEC 61000-4-4 (burst) 2 kV power line, 1kV data line |
| | IEC 61000-6-2 IEC 61000-4-5 (surge) power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line |
| | IEC 61000-6-2 IEC 61000-4-6 (immunity to conducted interference) 3 V (10 kHz ... 150 kHz), 10 V (150 kHz ... 80 MHz) |
| Noise immunity | EN 61000-6-2:2005 |

Noise emission

| | |
|-----------------------|--------------------|
| Standards/regulations | EN 55022 / Class B |
|-----------------------|--------------------|

Signaling

| | |
|----------------|--|
| Status display | LEDs:P1, P2, Fault, State, Error, LAN, WAN |
|----------------|--|

FL MGUARD RS2000 TX/TX-B - Router



2702139

<https://www.phoenixcontact.com/us/products/2702139>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19170406 |
| ECLASS-15.0 | 19170406 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001478 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43222600 |
|-------------|----------|

2702139

<https://www.phoenixcontact.com/us/products/2702139>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c), 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 029f96d5-46ab-48ff-a213-3ecde00aa543 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com