

# RCM-B/50/85-264V - Differential current monitoring



2806210

<https://www.phoenixcontact.com/us/products/2806210>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Residual current monitor in type B+ version for detecting smooth and pulsing AC and DC residual currents up to 100 kHz.

## Commercial data

Item number	2806210
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	CL05
Product key	CLB212
GTIN	4046356504928
Weight per piece (including packing)	203.5 g
Weight per piece (excluding packing)	203.5 g
Customs tariff number	90303310
Country of origin	DE

## Technical data

### Product properties

Product type	Evaluation unit
Insulation characteristics	
Overvoltage category	III
Pollution degree	2

### Electrical properties

Current consumption	< 6 VA
Nominal frequency $f_N$	50 Hz (60 Hz)
Nominal voltage $U_N$	85 V AC ... 264 V AC

### Typical characteristics

Max. required back-up fuse	16 A (B)
----------------------------	----------

### Indicator/remote signaling

Switching function	Changeover contact
Maximum operating voltage $U_{max. AC}$	230 V AC
Max. operating current $I_{max}$	5 A ( $\cos \phi > 0.9$ )
Max. required back-up fuse	4 A (gL)

### Typical characteristics

Rated response differential current $I_{dyn}$	3 A
Response differential current $I_{\Delta n}$	30, 100, 300, 1000, 3000 mA (adjustable)
Discrimination threshold main alarm	80 % ... 100 % (of the set response differential current $I_{\Delta n}$ )
Discrimination threshold pre-alarm	10 % ... 90 % (of the main alarm threshold, adjustable)
Response time for $2 \times I_{\Delta n}$	0.1 s ... 1 s (adjustable)
Rated voltage $U_n$	230 V AC
Differential current acquisition characteristic	Type B+ (DC up to 100 kHz)
Rated surge voltage resistance $U_{imp}$	4 kV

### Connection data

Connection method	Screw terminal blocks
Tightening torque	0.6 Nm
Conductor cross-section flexible min.	0.2 mm <sup>2</sup>
Conductor cross-section flexible max.	2.5 mm <sup>2</sup>
Min. conductor cross-section, flexible, with ferrule	0.25 mm <sup>2</sup>
Max. conductor cross-section, flexible, with ferrule	2.5 mm <sup>2</sup>
Conductor cross-section, rigid min.	0.2 mm <sup>2</sup>
Conductor cross-section, rigid max.	4 mm <sup>2</sup>

### Dimensions

# RCM-B/50/85-264V - Differential current monitoring



2806210

<https://www.phoenixcontact.com/us/products/2806210>

Dimensional drawing	
Width	71.6 mm
Height	89.7 mm
Depth	62.2 mm
Horizontal pitch	4 Div.

## Material specifications

Housing material	PC
------------------	----

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20 IP40 (distributor installation with cover)
Ambient temperature (operation)	-25 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

## Standards and regulations



Standards/specifications	DIN EN 62020
Standards/specifications	DIN EN 60664
Standards/specifications	DIN VDE 0664-400
Note	2012

## Mounting

Mounting type	DIN rail: 35 mm
Mounting position	any

Drawings

Dimensional drawing




# RCM-B/50/85-264V - Differential current monitoring

2806210

<https://www.phoenixcontact.com/us/products/2806210>



Circuit diagram



# RCM-B/50/85-264V - Differential current monitoring



2806210

<https://www.phoenixcontact.com/us/products/2806210>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)