

# MACX MCR-SL-CAC- 5-I - Current measuring transducer



2810612

<https://www.phoenixcontact.com/us/products/2810612>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Current measuring transducer for 1 A and 5 A AC, the output signal 0...20 mA or 4...20 mA, can be configured using a DIP switch with an operating mode indication through an LED

## Product description

The MACX MCR-SL-CAC-5-I(-UP) current measuring transducers convert sinusoidal alternating currents of 1 A or 5 A into standard analog signals 0...20 mA or 4...20 mA. The DIP switches, which can be accessed on the upper side of the housing, can be used to configure the input and output current.

The MACX MCR-SL-CAC-5-I current transducer contains a supply voltage range of 19.2 V DC to 30 V DC.

The MACX MCR-SL-CAC-5-I current transducer contains a long range version with a supply voltage range of 19.2 V AC/DC to 253 V AC/DC.

## Your advantages

- Input/output can be configured via DIP switches

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2810612       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | C444          |
| Product key                          | CMMA21        |
| GTIN                                 | 4046356153775 |
| Weight per piece (including packing) | 207.2 g       |
| Weight per piece (excluding packing) | 172.5 g       |
| Customs tariff number                | 85437090      |
| Country of origin                    | DE            |

# MACX MCR-SL-CAC- 5-I - Current measuring transducer



2810612

<https://www.phoenixcontact.com/us/products/2810612>

## Technical data

### Notes

#### Utilization restriction

|          |   |
|----------|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---|

### Product properties

|              |                              |
|--------------|------------------------------|
| Product type | Current measuring transducer |
|--------------|------------------------------|

#### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree     | 2   |

### Electrical properties

|   |   |
|---|---|
| Maximum power dissipation for nominal condition | 1.2 W   |
| Protective circuit                              | Surge protection; 35 V suppressor diode                   |
| Step response (10-90%)                          | ≤ 300 ms<br>200 ms  |
| Maximum temperature coefficient                 | < 0.02 %/K  |
| Temperature coefficient, typical                | < 0.015 %/K   |
| Maximum transmission error                      | ≤ 0.5 % (of nominal range value under nominal conditions) |
| Reverse polarity protection                     | yes   |
| Rated insulation voltage                        | 300 V AC (to earth)                                       |

#### Electrical isolation Input/output

|              |                       |
|--------------|-----------------------|
| Test voltage | 4 kV AC (50 Hz, 60 s) |
|--------------|-----------------------|

#### Electrical isolation Output/supply

|              |                       |
|--------------|-----------------------|
| Test voltage | 2 kV AC (50 Hz, 60 s) |
|--------------|-----------------------|

#### Supply

|                          |   |
|--------------------------|---|
| Nominal supply voltage   | 24 V DC -20 % ... +25 %                     |
| Supply voltage range     | 19.2 V DC ... 30 V DC                       |
| Max. current consumption | < 32 mA (at $U_B=24$ V DC, $I_{OUT}=20$ mA) |
| Power consumption        | < 0.9 W (at $U_B=24$ V DC, $I_{OUT}=20$ mA) |

### Input data

#### Measurement

|                           |  |
|---------------------------|--|
| Configurable/programmable | Via DIP switches   |
| Input current range       | 0 A AC ... 1 A AC (configurable)<br>0 A AC ... 5 A AC (configurable) |
| Voltage input signal      | ≤ 300 V AC   |
| Input impedance           | < 50 mΩ  |
| Overload capacity         | 2 x $I_N$ (continuous)   |

# MACX MCR-SL-CAC- 5-I - Current measuring transducer



2810612

<https://www.phoenixcontact.com/us/products/2810612>

|                                  |                           |
|----------------------------------|---------------------------|
| Surge strength                   | 20 x I <sub>N</sub> (1 s) |
| Nominal frequency f <sub>N</sub> | 50 Hz                     |
| Frequency measuring range        | 45 Hz ... 65 Hz           |
| Curve type                       | Sine                      |

## Output data

Signal: Current

|                                 |  |
|---------------------------------|--|
| Configurable/programmable       | Via DIP switches   |
| Open-circuit voltage            | 15 V   |
| Current output signal           | 0 mA ... 20 mA (configurable)<br>4 mA ... 20 mA (configurable) |
| Max. current output signal      | 25 mA  |
| Load/output load current output | < 500 Ω (20 mA)  |
| Ripple                          | < 10 mV <sub>PP</sub> (500 Ω / 20 mA)                          |
| Status display                  | LED red (error), LED green (ready)                             |

## Connection data

|                                  |   |
|----------------------------------|---|
| Connection method                | Screw connection                            |
| Stripping length                 | 8 mm  |
| Screw thread                     | M3  |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 24 ... 14                                   |
| Tightening torque                | 0.5 Nm ... 0.6 Nm                           |

## Interfaces

Data communication (bypass)

|                        |              |
|------------------------|--------------|
| Limit frequency (3 dB) | approx. 3 Hz |
|------------------------|--------------|

## Dimensions

Item dimensions

|        |          |
|--------|----------|
| Width  | 22.5 mm  |
| Height | 104 mm   |
| Depth  | 114.5 mm |

## Material specifications

|                  |                             |
|------------------|-----------------------------|
| Color            | gray (RAL 7042)             |
| Housing material | Polyamide PA non-reinforced |

## Environmental and real-life conditions

Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Degree of protection            | IP20             |
| Ambient temperature (operation) | -20 °C ... 65 °C |

# MACX MCR-SL-CAC- 5-I - Current measuring transducer



2810612

<https://www.phoenixcontact.com/us/products/2810612>

|   |                                      |
|---|--------------------------------------|
|   | -4 °F ... 149 °F                     |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C (-40 °F ... 185 °F) |
| Altitude                                | ≤ 2000 m                             |
| Permissible humidity (operation)        | 10 % ... 95 % (non-condensing)       |

## Approvals

### CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

### UL, USA/Canada

|                |                   |
|----------------|-------------------|
| Identification | UL 508 Recognized |
|----------------|-------------------|

## EMC data

|                               |  |
|-------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC directive                                       |
| Noise immunity                | EN 61000-6-2   |
| Note                          | When being exposed to interference, there may be minimal deviations. |

### Noise emission

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

### Electrostatic discharge

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-2 |
|-----------------------|--------------|

### Electromagnetic HF field

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-3 |
|-----------------------|--------------|

### Electromagnetic HF field

|          |             |
|----------|-------------|
| Comments | Criterion A |
|----------|-------------|

### Fast transients (burst)

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-4 |
|-----------------------|--------------|

### Fast transients (burst)

|          |             |
|----------|-------------|
| Comments | Criterion B |
|----------|-------------|

### Surge current load (surge)

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-5 |
|-----------------------|--------------|

### Surge current load (surge)

|          |             |
|----------|-------------|
| Comments | Criterion B |
|----------|-------------|

### Conducted interference

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-6 |
|-----------------------|--------------|

## Mounting

|                   |                   |
|-------------------|-------------------|
| Mounting type     | DIN rail mounting |
| Mounting position | any               |


# MACX MCR-SL-CAC- 5-I - Current measuring transducer

2810612

<https://www.phoenixcontact.com/us/products/2810612>

## Drawings

Dimensional drawing




# MACX MCR-SL-CAC- 5-I - Current measuring transducer



2810612


<https://www.phoenixcontact.com/us/products/2810612>

Application drawing



Current measurement

Circuit diagram



# MACX MCR-SL-CAC- 5-I - Current measuring transducer



2810612

<https://www.phoenixcontact.com/us/products/2810612>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2810612>



**cUL Recognized**  
Approval ID: E238705



**UL Recognized**  
Approval ID: E238705

# MACX MCR-SL-CAC- 5-I - Current measuring transducer



2810612

<https://www.phoenixcontact.com/us/products/2810612>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27210123 |
| ECLASS-15.0 | 27210123 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002475 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

# MACX MCR-SL-CAC- 5-I - Current measuring transducer



2810612

<https://www.phoenixcontact.com/us/products/2810612>

## Environmental product compliance

### EU RoHS

|   |              |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 1eec001d-65bf-4afc-a1db-0e8e9f1b3461 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)