

PSR-MM25-1NO-2DO-24DC-SP - Safety relay module



2702356

<https://www.phoenixcontact.com/us/products/2702356>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a version with a screw connection

Safety relay module for sensor-free zero-speed monitoring for 3- and 1-phase motors up to SIL 3, Cat. 3, PL e, 2-channel evaluation of the residual voltage of AC, three-phase, and DC motors, plug-in Push-in terminal block, width: 12.5 mm

Your advantages

- Monitoring of 1 and 3-phase AC or DC motors
- No additional sensors required
- Adjustable delay time from 0.5 s ... 20 s
- Adjustable switching threshold from 50 mV... 500 mV
- 1 enabling current path, 2 digital signal outputs
- Low housing width of just 12.5 mm
- Up to Cat. 3/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with EN IEC 62061

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2702356 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN01 |
| Product key | DNA241 |
| GTIN | 4055626133218 |
| Weight per piece (including packing) | 143.9 g |
| Weight per piece (excluding packing) | 143 g |
| Customs tariff number | 90328900 |
| Country of origin | DE |

Technical data

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Product properties

| | |
|--------------|-------------------------|
| Product type | Safety device |
| Application | Zero-speed safety relay |
| Control | 2-channel |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 2 |

Times

| | |
|-------------------------------|--|
| Typ. starting time with U_S | < 1 s |
| Response time | typ. 20 ms (at 50 Hz input frequency) |
| Delay time range | 0.5 s ... 20 s \pm 1 % (K1, K2 can be parameterized) |

Electrical properties

| | |
|--------------------------------|--|
| Nominal operating mode | 100% operating factor |
| Interfaces | Without sensor |
| Rated insulation voltage | 250 V AC |
| | 400 V AC with isolation paths between (L1/L2/L3) and the remaining current paths |
| | 690 V AC (with isolation paths within L1/L2/L3) |
| Rated surge voltage/insulation | Basic insulation 4 kV: between all current paths and housing |
| | Basic insulation 8 kV: between L1 and L2 between L1 and L3 between L2 and L3 |
| | Safe isolation, reinforced insulation 6 kV: between A1/A2 and 13/14 between MO/FO and 13/14 Safe isolation, reinforced insulation 8 kV: between L1/L2/L3 and A1/A2 between L1/L2/L3 and MO/FO between L1/L2/L3 and 13/14 |

Supply

| | |
|--|---|
| Designation | A1/A2 |
| Rated control circuit supply voltage U_S | 20.4 V DC ... 26.4 V DC |
| Rated control circuit supply voltage U_S | 24 V DC -15 % / +10 % |
| Rated control supply current I_S | typ. 50 mA |
| Power consumption at U_S | typ. 1.2 W |
| Inrush current | 5.6 A ($\Delta t = 400 \mu s$ at U_S) |

| | |
|--------------------|---|
| Filter time | 1 ms (at A1 in the event of voltage dips at U_S) |
| Protective circuit | Surge protection; Suppressor diode |
| | Reverse polarity protection |

Input data

Measurement

| | |
|----------------------|---|
| Input name | L1, L2, L3 |
| Number of inputs | 3 |
| Voltage input signal | max. 690 V AC/DC |
| Limit frequency | max. 3 kHz (At voltages $> 2 V_{RMS}$) |
| Current consumption | max. 0.35 mA |

Output data

Relay: Enabling current path (13/14)

| | |
|-----------------------------|--------------------------------------|
| Output description | safety-related N/O contacts |
| Number of outputs | 1 (undelayed) |
| Contact switching type | 1 enabling current path |
| Contact material | AgSnO ₂ |
| Switching voltage | min. 24 V AC/DC |
| | max. 250 V AC/DC |
| Switching power | min. 72 mW |
| Inrush current | min. 3 mA |
| | max. 5 A |
| Switching capacity | 5 A (AC15) |
| | 4 A (DC13) |
| Limiting continuous current | 5 A |
| Sq. Total current | 25 A ² (observe derating) |
| Switching frequency | max. 0.1 Hz |
| Mechanical service life | 10x 10 ⁶ cycles |
| Output fuse | 5 A gL/gG |

Signal: M0, F0

| | |
|--------------------------|-------------------------|
| Number of outputs | 2 (digital, PNP) |
| Voltage | 23 V DC ($U_S - 1 V$) |
| Current | max. 100 mA |
| Maximum inrush current | 500 mA |
| Short-circuit protection | Yes |

Connection data

Connection technology

| | |
|-----------|-----|
| pluggable | yes |
|-----------|-----|

Conductor connection

| | |
|-------------------|--------------------|
| Connection method | Push-in connection |
|-------------------|--------------------|

| | |
|---|--|
| Conductor cross-section rigid | 0.2 mm ² ... 1.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 1.5 mm ² |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve | 0.25 mm ² ... 1.5 mm ² (only together with CRIMPFOX 6) |
| Conductor cross-section, flexible, with ferrule, without plastic sleeve | 0.25 mm ² ... 1.5 mm ² (only together with CRIMPFOX 6) |
| Conductor cross-section AWG | 24 ... 16 |
| Stripping length | 8 mm |

Signaling

| | |
|----------------|-------------------|
| Status display | 4 x LED Bi-Colour |
|----------------|-------------------|

Dimensions

| | |
|--------|----------|
| Width | 12.5 mm |
| Height | 116.6 mm |
| Depth | 114.5 mm |

Material specifications

| | |
|------------------|-------------------|
| Color (Housing) | yellow (RAL 1018) |
| Housing material | PA |

Characteristics

Safety data

| | |
|----------------------------|---|
| Stop category (EN 60204-1) | 0 |
|----------------------------|---|

Safety data: EN ISO 13849

| | |
|------------------------|---|
| Performance level (PL) | e (4 A DC13; 5 A AC15; 17520 switching cycles/year) |
|------------------------|---|

Safety data: IEC 61508 - High demand

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 (4 A DC13; 5 A AC15; 17520 switching cycles/year) |
|------------------------------|---|

Safety data: EN IEC 62061

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Degree of protection | IP20 |
| Min. degree of protection of inst. location | IP54 |
| Ambient temperature (operation) | -20 °C ... 55 °C (observe derating) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Maximum altitude | max. 2000 m (Above sea level) |
| Max. permissible humidity (storage/transport) | 75 % (on average, 85% infrequently, non-condensing) |
| Max. permissible relative humidity (operation) | 75 % (on average, 85% infrequently, non-condensing) |
| Shock | 15g |
| Vibration (operation) | 10 Hz ... 150 Hz, amplitude 0.15 mm, 2g |

2702356

<https://www.phoenixcontact.com/us/products/2702356>

Approvals

CE


| | |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

Mounting

| | |
|-------------------|------------------------|
| Mounting type | DIN rail mounting |
| Assembly note | See derating curve |
| Mounting position | vertical or horizontal |

Drawings

Circuit diagram




Example application

2702356

<https://www.phoenixcontact.com/us/products/2702356>

Circuit diagram



Example application


PSR-MM25-1NO-2DO-24DC-SP - Safety relay module



2702356

<https://www.phoenixcontact.com/us/products/2702356>

Block diagram



Block diagram

2702356

<https://www.phoenixcontact.com/us/products/2702356>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702356>



UL Listed

Approval ID: E140324



cUL Listed

Approval ID: E140324



Functional Safety

Approval ID: 01/205/5492.02/24

2702356

<https://www.phoenixcontact.com/us/products/2702356>

Classifications

ECLASS

| | |
|-------------------|----------|
| ECLASS-13.0 | 27371811 |
| ECLASS-15.0 | 27371811 |
| ECLASS-15.0 ASSET | 27250101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001448 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

2702356

<https://www.phoenixcontact.com/us/products/2702356>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|----------------|
| CO2e kg | 38.633 kg CO2e |
|---------|----------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com