

PSR-MM20-2NO-1DO-24DC-SP - Safety relay module



2702375

<https://www.phoenixcontact.com/us/products/2702375>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety relay module for speed or zero-speed monitoring up to SIL 3, Cat. 4, PL e, suitable for connecting two proximity switches, pluggable Push-in terminal block, width: 17.5 mm

Product description

The locally configurable safety relay module is used for monitoring the zero-speed and speed of moving parts in systems and machines. To monitor movement, the safety relay module evaluates the signals of proximity switches.

Your advantages

- Up to Cat. 4/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with EN IEC 62061, SIL 3 in accordance with IEC 61508
- Compatible with a range of motion sensors
- Locally configurable
- Individually adjustable switching threshold in the range 0.5 Hz ... 315 Hz
- Low housing width of just 17.5 mm

Commercial data

Item number	2702375
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN01
Product key	DNA241
GTIN	4055626138169
Weight per piece (including packing)	160.7 g
Weight per piece (excluding packing)	135.46 g
Customs tariff number	85371098
Country of origin	DE

Technical data

Product properties

Product type	Safety device
Application	Zero-speed safety relay
	Over-speed safety relay
Control	2-channel
Relay type	Electromechanical relay with force-guided contacts in accordance with IEC/EN 61810-3

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Times

Typical response time	See Section "Maximum response time".
Response time	See Section "Maximum response time".
Typical release time	25 ms (When requested via A1; applicative deactivation via A1/A2 is not permitted)
Restart time	2.5 s (Boot time)
Start pulse length	min. 200 ms (manual start)
	max. 10 s (manual start)

Electrical properties

Maximum power dissipation for nominal condition	4 W ($U_B = 30\text{ V}$, $I_L = 6\text{ A}$)
Nominal operating mode	100% operating factor
Rated insulation voltage	250 V
Rated surge voltage/insulation	See data sheet, section "Insulation coordination".

Supply

Designation	A1/A2
Rated control circuit supply voltage U_S	24 V DC -20 % / +25 %
Rated control supply current I_S	typ. 70 mA
Power consumption at U_S	typ. 1.7 W
Inrush current	< 6 A ($\Delta t = 1\text{ ms}$ at U_S)
Filter time	1 ms (in the event of voltage dips)
Protective circuit	Serial protection against polarity reversal; Suppressor diode
Protection	1 A (slow-blow, required externally)

Input data

Digital: Start circuit (S34)

Description of the input	Non-safety-related, current sinking
	IEC 61131-2 type 3
Number of inputs	1
Input voltage range "0" signal	0 V DC ... 5 V DC

PSR-MM20-2NO-1DO-24DC-SP - Safety relay module



2702375

<https://www.phoenixcontact.com/us/products/2702375>

Input voltage range "1" signal	11 V DC ... 30 V DC
Input current range "0" signal	0 mA ... 1.5 mA
Max. permissible overall conductor resistance	150 Ω
Protective circuit	Suppressor diode
Current consumption	typ. 3 mA (at U_S)

Measurement

Input name	Proximity switch inputs IN1, IN2
Description of the input	Safety-related, current sinking/current sourcing
Number of inputs	2
Input voltage range "0" signal	Open circuit
Input voltage range "1" signal	15 V ... 30 V (Current, inward) 0 V ... 2 V (Current, outward)
Input current range "0" signal	Open circuit
Precision	$\pm 2\%$ (in reference to the parameterized limit value)
Limit frequency	max. 4 kHz (Minimum pulse duration: 45 μ s) min. 0.1 Hz (Minimum pulse duration: 45 μ s)
Duty factor	5 % ... 95 % (Push-pull operation, observe minimum pulse duration) 55 % ... 95 % (PNP operation, observe minimum pulse duration)
Hysteresis	20 %
Pulse width	45 μ s (Minimum pulse duration)
Max. permissible overall conductor resistance	150 Ω
Protective circuit	Suppressor diode
Current consumption	5 mA (Current, inward) -7 mA (Current, outward)

Output data

Relay: Enabling current paths (13/14, 23/24)

Output description	1 N/O contact each, safety-related, floating
Number of outputs	2
Contact switching type	2 enabling current paths
Contact material	AgSnO ₂
Switching voltage	min. 12 V AC/DC max. 250 V AC/DC
Switching power	min. 36 mW
Inrush current	min. 3 mA max. 6 A
Switching capacity	4 A (24 V (DC13)) 2 A (250 V (AC15))
Limiting continuous current	6 A
Sq. Total current	72 A ² (observe derating)
Switching frequency	0.1 Hz

PSR-MM20-2NO-1DO-24DC-SP - Safety relay module



2702375

<https://www.phoenixcontact.com/us/products/2702375>

Mechanical service life	10x 10 ⁶ cycles
Output fuse	6 A gL/gG

Signal: Digital signal output (MO)

Output description	non-safety-related
	PNP
Number of outputs	1
Voltage	approx. 22 V DC ($U_s - 2 \text{ V}$)
Current	max. 100 mA
Maximum inrush current	500 mA ($\Delta t = 100 \text{ ms}$ at U_s)
Ohmic load	min. 240 Ω
Switching frequency	0.1 Hz (Resistive load)
Protective circuit	Suppressor diode
Short-circuit protection	Yes
Discharging circuit	no

Signal: Analog signal output (AO+, AO-)

Output description	non-safety-related
	Analog
	Requirements on the connecting cables: 2-conductor, shielded, twisted pair
Number of outputs	1
Output voltage range	0 V ... 10.5 V $\pm 100 \text{ mV}$ (The tolerance may be greater under EMC influence)
Load/output load voltage output	$\geq 2 \text{ k}\Omega$
Protective circuit	Suppressor diode
Short-circuit protection	Yes
Signal rise time	1 ms ($R_L = 2 \text{ k}\Omega$, jump from 0 V to 10.5 V)
Control interval time	10 ms
Control time	max. 200 ms (For an accuracy of $\pm 500 \text{ mV}$)
	max. 400 ms (For an accuracy of $\pm 100 \text{ mV}$)
Max. permissible overall conductor resistance	6 Ω

Connection data

Connection technology

pluggable	yes
-----------	-----

Conductor connection

Connection method	Push-in connection
Conductor cross-section rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 1.5 mm ² (only together with CRIMPFOX 6)
Conductor cross-section, flexible, with ferrule, without plastic sleeve	0.25 mm ² ... 1.5 mm ² (only together with CRIMPFOX 6)
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

PSR-MM20-2NO-1DO-24DC-SP - Safety relay module



2702375

<https://www.phoenixcontact.com/us/products/2702375>

Signaling

Status display	6 x LED (green, red)
Operating voltage display	1 x LED (green, red)

Dimensions

Width	17.5 mm
Height	116.6 mm
Depth	114.5 mm

Material specifications

Color (Housing)	yellow (RAL 1018)
Housing material	PA

Characteristics

Safety data

Stop category (EN 60204-1)	0
----------------------------	---

Safety data: EN ISO 13849

Performance level (PL)	e (4 A DC13, 1095 switching cycles/year or 2 A DC13, 2 A AC15, 8760 switching cycles/year)
------------------------	--

Safety data: IEC 61508 - High demand

Safety Integrity Level (SIL)	3
------------------------------	---

Safety data: EN IEC 62061

Safety Integrity Level (SIL)	3
------------------------------	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Ambient temperature (operation)	-25 °C ... 60 °C (observe derating)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Maximum altitude	≤ 2000 m (Above sea level)
Max. permissible humidity (storage/transport)	75 % (on average, 85% infrequently, non-condensing)
Max. permissible relative humidity (operation)	75 % (on average, 85% infrequently, non-condensing)
Shock	15g
Vibration (operation)	10 Hz ... 150 Hz, 2g

Approvals

CE

Certificate	CE-compliant
-------------	--------------

Mounting

PSR-MM20-2NO-1DO-24DC-SP - Safety relay module




2702375

<https://www.phoenixcontact.com/us/products/2702375>

Mounting type	DIN rail mounting
Assembly note	See derating curve
Mounting position	vertical or horizontal

Drawings

Circuit diagram



Example application


PSR-MM20-2NO-1DO-24DC-SP - Safety relay module



2702375

<https://www.phoenixcontact.com/us/products/2702375>

Block diagram



Block diagram

PSR-MM20-2NO-1DO-24DC-SP - Safety relay module



2702375

<https://www.phoenixcontact.com/us/products/2702375>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702375>



cULus Listed

Approval ID: E140324



Functional Safety

Approval ID: 4420515124322



Functional Safety

Approval ID: 4478015124323

2702375

<https://www.phoenixcontact.com/us/products/2702375>

Classifications

ECLASS

ECLASS-13.0	27371811
ECLASS-15.0	27371811
ECLASS-15.0 ASSET	27250101

ETIM

ETIM 10.0	EC001448
-----------	----------

UNSPSC

UNSPSC 21.0	39122331
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)

EF3.1 Climate Change

CO2e kg	28.757 kg CO2e
---------	----------------