

# MCR-SLP-1-5-UI-0 - Current measuring transducer



2814359

<https://www.phoenixcontact.com/us/products/2814359>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



MCR passive current measuring transducer, for sinusoidal alternating currents 0..1 A AC/0..5 A AC, without switching output, output signal 0..10 V/0..20 mA

## Your advantages

- Loop-powered
- Measuring ranges 1 A and 5 A AC, reconnectable

## Commercial data

Item number	2814359
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C444
Product key	CMMA21
GTIN	4017918148447
Weight per piece (including packing)	246 g
Weight per piece (excluding packing)	210.4 g
Customs tariff number	85437090
Country of origin	DE

## Technical data

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Product properties

Product type	Current measuring transducer
--------------	------------------------------

#### Insulation characteristics

Overvoltage category	III
Pollution degree	2

### Electrical properties

Total error	$\leq 1.175\%$ (Temperature range)
Test voltage	3.5 kV
Measuring category	III
Step response (10-90%)	$< 200$ ms
Maximum temperature coefficient	$< 0.015\%/K$
Maximum transmission error	$< 0.5\%$ (of final value)
Rated insulation voltage	300 V AC (to earth)

### Input data

#### Signal

Configurable/programmable	no
---------------------------	----

#### Measurement

Input current range	0 A AC ... 1 A AC (Permitted continuous overload: 120%)
Overload capacity	$2 \times I_N$ (5 min. at 60°C ambient temperature)
Surge strength	50 A (1 s)
Permissible output range	$1.2 \times I_N$
Nominal frequency $f_N$	50 Hz
Frequency measuring range	45 Hz ... 60 Hz
Power dissipation	1.6 VA (at $I_A = 20$ mA)
Curve type	Sine

#### Measurement

Input current range	0 A AC ... 5 A AC (Permitted continuous overload: 120%)
Impulse form	Sine
Overload capacity	$2 \times I_N$ (5 min. at 60°C ambient temperature)
Surge strength	100 A (1 s)
Permissible output range	$1.2 \times I_N$
Nominal frequency $f_N$	50 Hz

# MCR-SLP-1-5-UI-0 - Current measuring transducer



2814359

<https://www.phoenixcontact.com/us/products/2814359>

Frequency measuring range	45 Hz ... 60 Hz
Power dissipation	2.2 VA (I = 20 mA)

## Output data

### Signal: Voltage

Voltage output signal	0 V ... 10 V
Max. voltage output signal	20 V
Load/output load voltage output	> 100 k $\Omega$
Ripple	< 50 mV <sub>PP</sub>

### Signal: Current

Current output signal	0 mA ... 20 mA
Max. current output signal	30 mA
Load/output load current output	< 750 $\Omega$ < 250 $\Omega$ (when current and voltage outputs are used simultaneously)
Ripple	< 50 mV <sub>PP</sub>
Residual ripple, in reference to the measured value	0.5 % (pp of measured value)

## Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 14

## Dimensions

### Item dimensions

Width	22.5 mm
Height	99 mm
Depth	114.5 mm

## Material specifications

Color	green (RAL 6021)
Housing material	Polyamide PA non-reinforced

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 80 °C (non-condensing)
Altitude	< 2000 m
Permissible humidity (operation)	10 % ... 95 % (non-condensing)

# MCR-SLP-1-5-UI-0 - Current measuring transducer



2814359

<https://www.phoenixcontact.com/us/products/2814359>

## Approvals

CE

Certificate	CE-compliant
-------------	--------------

## EMC data

Electromagnetic compatibility	Conformance with EMC directive
Noise immunity	EN 61000-6-2
Note	When being exposed to interference, there may be minimal deviations.

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

## Standards and regulations

Standards/regulations	IEC 61010-2-030
-----------------------	-----------------

## Mounting


Mounting type	DIN rail mounting
Mounting position	< 50 °C: any; > 50 °C: vertical (installation on horizontal DIN rail)

# MCR-SLP-1-5-UI-0 - Current measuring transducer


2814359

<https://www.phoenixcontact.com/us/products/2814359>

## Drawings



Circuit diagram



# MCR-SLP-1-5-UI-0 - Current measuring transducer



2814359

<https://www.phoenixcontact.com/us/products/2814359>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2814359>



**cUL Recognized**  
Approval ID: E238705



**UL Recognized**  
Approval ID: E238705

# MCR-SLP-1-5-UI-0 - Current measuring transducer



2814359

<https://www.phoenixcontact.com/us/products/2814359>

## Classifications

### ECLASS

ECLASS-13.0	27210123
ECLASS-15.0	27210123

### ETIM

ETIM 10.0	EC002475
-----------	----------

### UNSPSC

UNSPSC 21.0	39121000
-------------	----------

2814359

<https://www.phoenixcontact.com/us/products/2814359>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	681206d3-8832-4e1f-bb7b-9720cb9d9362

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)