

ST-REL7-HG 24/4X21 - Relay connectors

2827139

<https://www.phoenixcontact.com/us/products/2827139>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay connector, equipped with Hengstler miniature round relay, contacts (AgSnO₂+Au): small to large loads, 4 changeover contacts, input voltage 24 V DC, with LED display, pluggable into basic terminal blocks

Commercial data

Item number	2827139
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	C460
Product key	DK61B2
GTIN	4017918078140
Weight per piece (including packing)	99.25 g
Weight per piece (excluding packing)	92 g
Customs tariff number	85364190
Country of origin	DE

ST-REL7-HG 24/4X21 - Relay connectors



2827139

<https://www.phoenixcontact.com/us/products/2827139>

Technical data

Product properties

Product type	Relay Module
Operating mode	100% operating factor
Mechanical service life	approx. 10^7 cycles

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Data management status

Date of last data management	01.04.2026
------------------------------	------------

Electrical properties

Maximum power dissipation for nominal condition	0.96 W
Test voltage (Winding/contact)	2 kV AC (50 Hz, 1 min., winding/contact)
Test voltage (Changeover contact/changeover contact)	2 kV AC (50 Hz, 1 min., changeover contact/changeover contact)

Input data

Coil side

Nominal input voltage U_N	24 V DC
Input voltage range	19.2 V DC ... 26.4 V DC (20 °C)
Drive and function	monostable
Drive (polarity)	polarized
Typical input current at U_N	40 mA
Typical response time	15 ms (with DC)
Typical release time	15 ms (with DC)
Protective circuit	Damping diode, polarity protection; Damping diode, polarity protection diode
Operating voltage display	yes

Output data

Switching

Contact switching type	4 changeover contacts
Type of switch contact	Single contact
Contact material	AgSnO, hard gold-plated
Maximum switching voltage	250 V AC/DC
Limiting continuous current	6 A
Maximum inrush current	6 A
Interrupting rating (ohmic load) max.	120 W (at 24 V DC) 180 W (at 48 V DC) 105 W (at 60 V DC) 60 W (at 110 V DC)

ST-REL7-HG 24/4X21 - Relay connectors



2827139

<https://www.phoenixcontact.com/us/products/2827139>

	90 W (at 220 V DC)
	1250 VA (for 250 V AC)

Dimensions

Item dimensions

Width	45.6 mm
Height	33 mm
Depth	66.5 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	IEC 60664A
	DIN VDE 0110
	DIN VDE 0109-11, draft
	DIN VDE 0160 (in relevant parts)

Mounting

Mounting type	Plug-in mounting
---------------	------------------


ST-REL7-HG 24/4X21 - Relay connectors

2827139

<https://www.phoenixcontact.com/us/products/2827139>

Drawings

Circuit diagram



ST-REL7-HG 24/4X21 - Relay connectors



2827139

<https://www.phoenixcontact.com/us/products/2827139>

Classifications

ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

ETIM

ETIM 10.0	EC001437
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

ST-REL7-HG 24/4X21 - Relay connectors



2827139

<https://www.phoenixcontact.com/us/products/2827139>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d412176e-d8eb-467b-bf0e-c28383ea1542

EF3.1 Climate Change

CO2e kg	11.376 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com