

PLD M 260 W-85/95 540/D40/SC - LED machine light



2702935

<https://www.phoenixcontact.com/us/products/2702935>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



LED machine light, 24 V DC, emission angle (vertical/Horizontal): 85 °/95 °, length: 540 mm, diameter: 40 mm, degree of protection: IP67, can be swiveled, resistant to coolants and lubricants, can be switched in series

Product description

This LED machine light is designed to provide illumination inside or on machinery. You can use the light in harsh environments. This is possible thanks to the following properties: - High type of protection - Resistance to common cooling agents and lubricants - Resistance to vibrations and shock - 4 mm-thick safety glass The small diameter of just 40 mm enables mounting even where space is at a premium. Mounting is by means of holders or brackets (neither of which are supplied as standard) in which the light can swivel and the lighting can therefore be optimally aligned. To reduce the cabling effort for longer machines, the lights can be switched in series.

Your advantages

- Space saving, thanks to the small diameter
- Plug-in supply line enables free choice of the cable length as well as quick and easy installation
- Focused illumination, thanks to swivel action
- IP67 protection and resistance to cooling agents and lubricants enables use in machine tools
- Can be used at high temperatures and can be subjected to strong vibrations and shocks
- Safety glass enables use even in environments with potential mechanical strain
- Minimal wiring effort, thanks to series connection
- ETL approval permits use on the North American market
- Particularly economical thanks to energy-efficient LED technology and an LED service life of at least 60000 h

Commercial data

Item number	2702935
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR08
Product key	DRL222
GTIN	4055626443782
Weight per piece (including packing)	1,000 g
Weight per piece (excluding packing)	1,028 g
Customs tariff number	94054239
Country of origin	DE

PLD M 260 W-85/95 540/D40/SC - LED machine light



2702935

<https://www.phoenixcontact.com/us/products/2702935>

Technical data

Notes

Order information:	The PLD M-ME MC/D40 mounting holder (item no. 2702492) or the PLD M-ME MB/D40 mounting bracket (item no. 2702527) is required to mount the light.
--------------------	---

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Machine light
Application	Machine tool
Mounting position	any
Special properties	can be swiveled with mounting accessories resistant to coolants and lubricants can be switched in series

Electrical properties

Supply: Module electronics

Connection method	M12 connector, A-coded
Number of positions	4
Permissible conductor cross-section	min. 0.34 mm ²
Supply voltage	24 V DC
Supply voltage range	20 V DC ... 28 V DC
Current consumption	typ. 0.67 A (at 24 V DC)
Power consumption	approx. 16 W (at 24 V DC)
Protective circuit	Surge protection; Varistor and suppressor diode, 36 V DC Reverse polarity protection; Polarity protection diode

Connection data

Connection method	M12 connector, A-coded
-------------------	------------------------

Signaling

Light properties

Source of light type	LED
Number of LEDs	42
Color temperature	5000 K
Color rendering index	80
Luminous flux	approx. 1680 lm (Net luminous flux)
Luminous efficacy	approx. 105 lm/W
Illumination	max. 732 lx (Distance of 1 m) min. 326 lx (Distance of 1 m over 1 m ² area)
Average illumination	541 lx (Distance of 1 m over 1 m ² area)

PLD M 260 W-85/95 540/D40/SC - LED machine light



2702935

<https://www.phoenixcontact.com/us/products/2702935>

Emission angle	85 ° (C0-C180) 95 ° (C90-C270)
Ordinance	Delegated Regulation (EU) 2019/2015
Energy efficiency class	E (3 light sources)
Note	This product contains energy efficiency class E light sources.

Dimensions

Dimensional drawing	
Width	40 mm
Height	30 mm
Length	540 mm
Diameter	40 mm
Note on dimensions	Length without M12 flush-type connector

Material specifications

Color (Housing)	aluminum color black (RAL 9005)
Material	Anodized aluminum (Light housing) Single-pane safety glass (ESG, thermally toughened float glass) (Pane)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 50 °C
Degree of protection	IP67
Air pressure (operation)	69 kPa ... 102 kPa
Air pressure (storage/transport)	69 kPa ... 102 kPa
Ambient temperature (storage/transport)	-20 °C ... 75 °C
Permissible humidity (operation)	95 % (non-condensing)
Permissible humidity (storage/transport)	95 % (non-condensing)

Mechanical test

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	4g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	50g

Energy labeling

Ordinance	Delegated Regulation (EU) 2019/2015
Note	The EPREL entry can be searched for with the registration number (https://eprel.ec.europa.eu/screen/home) The EPREL entry can be searched for with the model ID (https://eprel.ec.europa.eu/screen/product/lightsources) 1097904

PLD M 260 W-85/95 540/D40/SC - LED machine light



2702935

<https://www.phoenixcontact.com/us/products/2702935>

Registration number	1097908
	1097905

Energy labeling (Light source 1)

Registration number	1097904
Model ID	629129
Energy efficiency class	E
Number of light sources	1

Energy labeling (Light source 2)

Registration number	1097908
Model ID	655303
Energy efficiency class	E
Number of light sources	1

Energy labeling (Light source 3)

Registration number	1097905
Model ID	639131
Energy efficiency class	E
Number of light sources	1

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	Screw mounting (See necessary accessories for mounting accessories)
Mounting position	any

PLD M 260 W-85/95 540/D40/SC - LED machine light


2702935

<https://www.phoenixcontact.com/us/products/2702935>



Drawings

Dimensional drawing



2702935

<https://www.phoenixcontact.com/us/products/2702935>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702935>



ETLus

Approval ID: LV-Lighting-Systems



cETL

Approval ID: Luminaires



EAC

Approval ID: TR_TS_D_12879-22

2702935

<https://www.phoenixcontact.com/us/products/2702935>

Classifications

ECLASS

ECLASS-13.0	27110345
ECLASS-15.0	27110345

ETIM

ETIM 10.0	EC000348
-----------	----------

UNSPSC

UNSPSC 21.0	32151500
-------------	----------

2702935

<https://www.phoenixcontact.com/us/products/2702935>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	523913cb-1026-4527-9996-28f558ee391b

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com