

PSR-CT-C-SEN-1-8 - Safety switch sensor



2702972

<https://www.phoenixcontact.com/us/products/2702972>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Proximity safety circuit up to Cat. 4, PL e (EN ISO 13849), SIL 3 (IEC 61508), unicode sensor with RFID coding, model 4 (EN ISO 14119), automatic or manual start, integrated diagnostics, 24 V DC supply, IP69K, M12 connector

Product description

The PSR-CT safety circuit consists of a combination of a PSR-CT-...-SEN-1-8 sensor with varying coding types and a coded PSR-CT-C-ACT actuator. It provides maximum tamper protection and the highest level of safety in accordance with EN ISO 14119. The PSR-CT safety circuit is available with the following types of coding: **Fixcode:** For the sensor to detect the actuator, the actuator must first be associated with the sensor via a learning process. The learning process can only be completed once. The sensor and actuator are then permanently assigned to each other by their coding. Safety circuits with fixcode evaluation achieve a **high coding level**. **Unicode:** For the sensor to detect the actuator, the actuator must first be assigned to the sensor via a learning process. The learning process for a new actuator can be repeated any number of times. The sensor only detects the last learned actuator. Safety circuits with unicode evaluation achieve a **high coding level**. **Multicode:** The sensor detects every actuator of the approved type. No specific actuator code can be assigned. Safety circuits with multicode evaluation achieve a **low coding level**.

Your advantages

- Integrated reset function on the switch
- 4 actuation settings, 3 travel directions
- Tamper protection via RFID transponder technology
- Rapid diagnostics, thanks to comprehensive status information
- Consistent M12 connection technology for convenient installation
- Safe series connection in accordance with EN ISO 14119
- Flexible use, thanks to compact design
- Safe, cost-effective complete solution

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2702972 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN04 |
| Product key | DNA611 |
| GTIN | 4055626446899 |
| Weight per piece (including packing) | 40.8 g |
| Weight per piece (excluding packing) | 40.8 g |
| Customs tariff number | 85365019 |

PSR-CT-C-SEN-1-8 - Safety switch sensor



2702972

<https://www.phoenixcontact.com/us/products/2702972>

| | |
|-------------------|----|
| Country of origin | DE |
|-------------------|----|

Technical data

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Product properties

| | |
|--|---|
| Product type | Safety switches |
| Product family | PSR-CT |
| Technology | Transponder |
| Application | Safety door monitoring Position monitoring |
| Design in accordance with EN ISO 14119 | 4 |
| Encoding level in accordance with EN ISO 14119 | high |

Insulation characteristics

| | |
|---------------------|-----|
| Protection class | III |
| Degree of pollution | 3 |

Times

| | |
|------------------|--|
| Discrepancy time | max. 10 ms (between the safety outputs) |
| Switch-on delay | typ. 5 s (after switching U_B on) |
| Switch-on time | max. 400 ms (for the safety outputs) |
| Risk time | max. 125 ms (Stand-alone device) |
| Test pulses | typ. 300 μ s (Test pulse duration) approx. 100 ms (Test pulse interval) |
| Delay time | typ. 10 ms (Risk time delay per device) |

Electrical properties

| | |
|--------------------------|--|
| Switching frequency | max. 1 Hz |
| Short-circuit current | typ. 100 A (conditional short-circuit current) |
| Switching frequency | max. 1 Hz |
| Rated insulation voltage | max. 300 V |
| Rated surge voltage | max. 1.5 kV |

Supply

| | |
|------------------------|---|
| Supply voltage | 24 V DC \pm 15 % (PELV, controlled, residual ripple < 5%) |
| Current consumption | max. 40 mA |
| Protection | min. 0.25 A (to be performed externally) max. 8 A (to be performed externally) |
| Contact switching type | 2 safe digital outputs |

Output data

Signal

PSR-CT-C-SEN-1-8 - Safety switch sensor



2702972

<https://www.phoenixcontact.com/us/products/2702972>

| | |
|---------------------|------------------------------|
| Designation | DGN |
| Output description | p-wired |
| Number of outputs | 1 |
| Output voltage | min. ($U_B - 1.5$ V (HIGH)) |
| | max. (U_B (HIGH)) |
| | min. 0 V DC (LOW) |
| | max. 1 V DC (LOW) |
| Current | min. 1 mA |
| | max. 50 mA |
| Short-circuit-proof | yes |

Safety output

| | |
|---|---|
| Designation | FO1A, FO1B |
| Output description | Semiconductor outputs, p-wired |
| Number of outputs | 2 |
| Output voltage | min. ($U_B - 1.5$ V (HIGH FO1A, FO1B)) |
| | max. (U_B (HIGH FO1A, FO1B)) |
| | min. 0 V DC (LOW FO1A/FO1B) |
| | max. 1 V DC (LOW FO1A/FO1B) |
| Switching current | min. 1 mA (per safety output) |
| | max. 150 mA (per safety output) |
| Residual current | ≤ 0.25 mA |
| Utilization category in accordance with IEC 60947-5-2 | 150 mA (24 V (DC13)) |
| Short-circuit-proof | yes |
| Note on protection circuit | NOTE: Protect the outputs under inductive loads with a freewheeling diode. |

Connection data

Connection technology

| | |
|-----------------------|---------------|
| Connection technology | M12 connector |
| pluggable | no |
| Number of positions | 8 |

Conductor connection

| | |
|-----------------------|---------------|
| Connection method | Connector |
| Connection technology | M12 connector |
| Number of positions | 8 |

Signaling

| | |
|----------------|--------|
| Status display | 2 LEDs |
|----------------|--------|

Dimensions

PSR-CT-C-SEN-1-8 - Safety switch sensor



2702972

<https://www.phoenixcontact.com/us/products/2702972>

| | |
|---------------------|---------|
| Dimensional drawing | |
| Width | 26.5 mm |
| Height | 40 mm |
| Depth | 18 mm |

Material specifications

| | |
|------------------|-------------------|
| Color (Housing) | yellow (RAL 1018) |
| Housing material | PBT |

Characteristics

Safety data: EN ISO 13849

| | |
|------------------------|---|
| Performance level (PL) | e |
|------------------------|---|

Safety data: IEC 61508 - High demand

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP65/IP67/IP69/IP69K IP67 (with SAC cabling) |
| Ambient temperature (operation) | -25 °C ... 55 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Vibration (operation) | in accordance with EN 60947-5-2 |

Approvals

Conformity/Approvals

| | |
|-----------------|--------------|
| EMC conformance | EN 60947-5-3 |
|-----------------|--------------|

Mounting

| | |
|-------------------|--|
| Mounting type | Mounting panel |
| Assembly note | Note EN ISO 14119 max. tightening torque to secure: 0.8 Nm |
| Mounting position | any |
| Minimum distance | 140 mm (between two safety circuits) 7 mm (between sensor and actuator when traveling in the Y-direction) |

PSR-CT-C-SEN-1-8 - Safety switch sensor





2702972

<https://www.phoenixcontact.com/us/products/2702972>

Drawings


Dimensional drawing



PSR-CT-C-SEN-1-8 - Safety switch sensor

2702972

<https://www.phoenixcontact.com/us/products/2702972>



Application drawing




PSR-CT-C-SEN-1-8 - Safety switch sensor

2702972

<https://www.phoenixcontact.com/us/products/2702972>

Connection diagram



PSR-CT-C-SEN-1-8 - Safety switch sensor



2702972

<https://www.phoenixcontact.com/us/products/2702972>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702972>



UL Listed

Approval ID: E196162



cUL Listed

Approval ID: E196162



Functional Safety

Approval ID: Z10 029429 0033

FCC

Approval ID: YG3-PSR1

Industry Canada

Approval ID: 4720B-PSR1

PSR-CT-C-SEN-1-8 - Safety switch sensor



2702972

<https://www.phoenixcontact.com/us/products/2702972>

Classifications

ECLASS

| | |
|-------------------|----------|
| ECLASS-15.0 | 27274601 |
| ECLASS-13.0 | 27274601 |
| ECLASS-15.0 ASSET | 27250101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003015 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 32151800 |
|-------------|----------|

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c), 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | Lead titanium trioxide(CAS: 12060-00-3) |
| | Lead(CAS: 7439-92-1) |
| SCIP | 176081b5-cb7c-4f70-a6c0-37a59f7b2b72 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 9.862 kg CO2e |
|---------|---------------|