

FL IBS SC/I-T - Ethernet gateway

2831060

<https://www.phoenixcontact.com/us/products/2831060>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

INTERBUS Ethernet gateway, Generation 4



Commercial data

Item number	2831060
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR14
Product key	DRECAC
GTIN	4017918818531
Weight per piece (including packing)	333.1 g
Weight per piece (excluding packing)	316.4 g
Customs tariff number	85389091
Country of origin	DE

Technical data

Product properties

Type	Stand-alone
------	-------------

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

System properties

INTERBUS-Master

Amount of process data	256 words (4096 binary inputs/outputs)
Number of supported devices	512 (of which 256 are remote bus devices/segments)
Number of devices with parameter channel	62

INTERBUS-Slave

Amount of process data	256 words (4096 binary inputs/outputs)
Number of PCP words	256 words (4096 binary inputs/outputs)

Functionality

Basic functions	Ethernet: Terminal equipment, complies with IEEE 802.3, TCP/IP protocol, BootP and TFTP-capable
	INTERBUS: Generation 4 master

System requirements

Supported browsers	Netscape Communicator versions 4.5 and up or Internet Explorer versions 4.01 and up
--------------------	---

Electrical properties

Power consumption	typ. 4.8 W
Maximum power dissipation for nominal condition	4 W
Test section	500 V AC 50 Hz 1 min
Transmission medium	Copper

Supply

Supply voltage	24 V DC (via COMBICON; max. conductor cross-section 2.5 mm ²)
Supply voltage range	18.5 V DC ... 30.2 V DC
Power supply connection	Via COMBICON, max. conductor cross-section 2.5 mm ²
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Typical current consumption	200 mA (to U _S)

Connection data

Connection method	10/100 Base-T(X), auto negotiation
-------------------	------------------------------------

Interfaces

Ethernet

Connection method	1 port 10/100Base-T(X), auto negotiation
Transmission length	100 m

INTERBUS master interface

Connection method	9-pos. D-SUB socket strip
-------------------	---------------------------

Diagnostics INTERBUS

Connection method	6-pos. MINI-DIN female connector
-------------------	----------------------------------

Signaling

Status display	Two-digit, seven-segment display and LEDs: UL (communications voltage), COL (collision), Link, Receive, Transmit, Full Duplex, 100 Mbps Wirespeed, INTERBUS: RDY/RUN, BSA, FAIL, PF
----------------	---

Dimensions

Width	45 mm
Height	99 mm
Depth	117 mm

Material specifications

Color	green
-------	-------

Mechanical tests

Shock in accordance with EN 60068-2-27/IEC 60068-2-27	: Operation: 25g, 11 ms duration, semi-sinusoidal shock impulse
	: Storage/Transport: 50g, 11 ms duration, semi-sinusoidal shock impulse
Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	: Operation/Storage/Transport: 5g, 150 Hz, Criterion 3
Free fall in accordance with IEC 60068-2-32	: 1 m

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	30 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	30 % ... 95 % (non-condensing)
Air pressure (operation)	86 kPa ... 108 kPa (1500 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)
Resistance to gases that may endanger the functions, in acc. with DIN 40046-36, DIN 40046-37	Sulfur dioxide (SO ₂) 10 ±0.3 cm ³ /m ³ , hydrogen sulfide (H ₂ S) 1 ±0.3 cm ³ /m ³ , at 25 °C and 75% humidity and exposure of four days

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC IEC 61000-6-2 IEC 61000-4-2 (ESD) Criterion B
-------------------------------	---

FL IBS SC/I-T - Ethernet gateway



2831060

<https://www.phoenixcontact.com/us/products/2831060>

Conformance with EMC directives	IEC 61000-6-2 IEC 61000-4-3 (immunity to radiated interference) Criterion A
	IEC 61000-6-2 IEC 61000-4-4 (burst) Criterion B
	IEC 61000-6-2 IEC 61000-4-5 (surge) Criterion B
	IEC 61000-6-2 IEC 61000-4-6 (immunity to conducted interference) Criterion A
	IEC 61000-6-2 EN 55011 (emitted interference) Class A
Noise immunity	EN 61000-6-2:2005

Noise emission

Standards/regulations	EN 50081-2
-----------------------	------------

Standards and regulations

Free from substances that could impair the application of coating	In acc. with VW specification
---	-------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

FL IBS SC/I-T - Ethernet gateway



2831060

<https://www.phoenixcontact.com/us/products/2831060>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com