

# ME DH 36 NS 35 KMGY - Spacer




2706292

<https://www.phoenixcontact.com/us/products/2706292>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Spacers, for protection of the input or output contacts for DIN rail NS 35, width [B] 36 mm



## Your advantages

- Easy installation

## Commercial data

Item number	2706292
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AC08
Product key	ACHACZ
GTIN	4046356517508
Weight per piece (including packing)	14.3 g
Weight per piece (excluding packing)	14.3 g
Customs tariff number	39269097
Country of origin	DE

# ME DH 36 NS 35 KMGY - Spacer



2706292

<https://www.phoenixcontact.com/us/products/2706292>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Mounting material
Housing type	DIN rail housing
Housing series	ME
Ventilation openings present	no

### Material specifications

Color (Housing)	light gray (RAL 7035)
Material Housing	PA
Flammability rating according to UL 94	V0
Surface characteristics	untreated

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

# ME DH 36 NS 35 KMGY - Spacer



2706292

<https://www.phoenixcontact.com/us/products/2706292>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME DH 36 NS 35 KMGY - Spacer



2706292

<https://www.phoenixcontact.com/us/products/2706292>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)