UTA 130 - DIN rail adapter

2706412

https://www.phoenixcontact.com/us/products/2706412

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Universal DIN rail adapter for screwing on switchgear



Commercial data

Item number	2706412
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AC07
Product key	ACGEAD
GTIN	4017918822743
Weight per piece (including packing)	150.8 g
Weight per piece (excluding packing)	146.7 g
Customs tariff number	79070000
Country of origin	DE

Technical data

Product properties

Product type	DIN rail adapter
Housing type	DIN rail adapter
Product family	UTA
Type	Fastening holes provided, integrated foot catch

Dimensions

Width	52 mm
Height	130 mm
Depth	9.6 mm

Material specifications

Housing material	Die-cast zinc

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm (10 Hz ... 60.1 Hz)
Acceleration	5g (60.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

Mounting

Mounting type	DIN rail mounting

Classifications

ECLASS

ECLASS-13.0	27370419
ECLASS-15.0	27370419

ETIM

ETIM 10.0	EC001024

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.378 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com