

EMG150-LG/MSTB BK - Electronics housing

2707712

<https://www.phoenixcontact.com/us/products/2707712>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronic housing, for PCB insertion, without screw connection terminal blocks and cover, with lateral opening for connector

The figure shows a version of the product

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2707712 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Product key | ACHCBA |
| GTIN | 4017918905088 |
| Weight per piece (including packing) | 118.19 g |
| Weight per piece (excluding packing) | 100.63 g |
| Country of origin | DE |

2707712

<https://www.phoenixcontact.com/us/products/2707712>

Technical data

Product properties

| | |
|---------------------|-------------------|
| Product type | Complete housing |
| Housing type | Component housing |
| Housing series | EMG |
| Product family | EMG...-LG |
| Number of positions | 58 |

Dimensions

| | |
|------------------|--------|
| Width | 150 mm |
| Height NS 35/7,5 | 55 mm |
| | 83 mm |
| Depth | 75 mm |

Material specifications

| | |
|----------------------------------------|---------------------------------------|
| Color | black (RAL 9005) |
| Flammability rating according to UL 94 | V0 |
| Housing material | Polycarbonate, glass-fiber-reinforced |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

EMG150-LG/MSTB BK - Electronics housing



2707712

<https://www.phoenixcontact.com/us/products/2707712>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

EMG150-LG/MSTB BK - Electronics housing



2707712

<https://www.phoenixcontact.com/us/products/2707712>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

| | |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com