

# PSM-SET-SCRJ-DUP/2-POF - FO connectors



2708656

<https://www.phoenixcontact.com/us/products/2708656>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

FO connectors, degree of protection: IP20, number of positions: 2, MM, material: Metal, connection method: Push-Pull, cable outlet: straight



SC-RJ

## Product description

SC-RJ fiber optic connector, IP20, duplex, with fast connection technology, for polymer fiber 980/1000 µm, for individual wire diameter 2.2 mm

## Your advantages

- Compact design, thanks to SC-RJ pin connector pattern
- Outstanding transmission properties
- Suitable for quick and easy field assembly or repair
- No bonding or polishing
- Flexible application, thanks to reusable connector

## Commercial data

Item number	2708656
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIAA
GTIN	4046356123327
Weight per piece (including packing)	37.42 g
Weight per piece (excluding packing)	29.504 g
Customs tariff number	85367000
Country of origin	DE

2708656

<https://www.phoenixcontact.com/us/products/2708656>

## Technical data

### Product properties

Product type	Fiber optic connector (cable side)
Application	neutral
Type	SC-RJ
Number of positions	2
Connection profile	SC-RJ
Cable outlet	straight

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Attenuation	< 1.5 dB (Insertion attenuation)
Transmission medium	FO
Transmission characteristics (category)	MM

### Connection data

Connection method	Push-Pull
-------------------	-----------

### Dimensions

#### Mechanical characteristics

Ferrule diameter	2.50 mm
------------------	---------

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	nickel-plated

### Cable/line

Cable type	Plastic fiber
External cable diameter	2.2 mm ... 2.2 mm

#### FO cable

Number of fibers	2
Fiber	POF, PCF, GOF
Fiber type	GOF, PCF, POF
Transmission medium	FO

### Characteristics

Attenuation	< 1.5 dB (Insertion attenuation)
-------------	----------------------------------

### Environmental and real-life conditions

# PSM-SET-SCRJ-DUP/2-POF - FO connectors



2708656


<https://www.phoenixcontact.com/us/products/2708656>

## Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Ambient temperature (assembly)	0 °C ... 50 °C

Drawings

Schematic diagram



# PSM-SET-SCRJ-DUP/2-POF - FO connectors



2708656

<https://www.phoenixcontact.com/us/products/2708656>

## Classifications

### ECLASS

ECLASS-13.0	19170122
ECLASS-15.0	19170122

### ETIM

ETIM 10.0	EC001122
-----------	----------

### UNSPSC

UNSPSC 21.0	43223300
-------------	----------

# PSM-SET-SCRJ-DUP/2-POF - FO connectors



2708656

<https://www.phoenixcontact.com/us/products/2708656>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)